OptoSupply
Light It Up

3mm Deluxe Power White LED

OSW54L3131P


■Features

- High Luminous LEDs
- 3mm Standard Directivity
- Long Lifetime Operation
- UV Resistant Epoxy
- Water Clear Type

■Applications

- Electronic Signs And Signals
- Small Area Illuminations
- Back Lighting
- Other Lighting

■Outline Dimension




■Absolute Maximum Rating (Ta=25℃)

Item	Symbol	Value	Unit
DC Forward Current	I_F	50	mA
Pulse Forward Current#	I_{FP}	100	mA
Reverse Voltage	V_R	5	V
Power Dissipation	P_D	180	mW
Operating Temperature	Topr	-30 ~ +85	℃
Storage Temperature	Tstg	-40 ~ +100	℃
Lead Soldering Temperature	Tsol	260℃/5sec	-

#Pulse width Max 10ms , Duty ratio max 1/10

■Directivity



■Electrical -Optical Characteristics (Ta=25℃)

Item	Symbol	Condition	Min.	Typ.	Max.	Unit
DC Forward Voltage*	V_F	I_F=50mA	2.8	3.1	3.6	V
DC Reverse Current	I_R	V_R=5V	-	-	10	μA
Luminous Intensity*	Iv	I_F=50mA	30000	36000	-	mcd
Color Temperature*3	CCT	I_F=50mA	-	10000	-	K
Chromaticity Coordinates*	x	I_F=50mA	-	0.27	-	
	y	I_F=50mA	-	0.28	-	
50% Power Angle	$2\theta_{1/2}$	I_F=50mA	-	30	-	deg

*1 Tolerance of measurements of chromaticity coordinate is ±10%
*2 Tolerance of measurements of luminous intensity is ±15%
*3 Tolerance of measurements of forward voltage is ±0.1V

ATTENTION
OBSERVE PRECAU
ELECTROSTATIC
SENSITIVE DEVICE

Downloaded from Arrow.com.