


RESISTANCE @ +25°C = 1,000 Ω ± 10%
RESISTANCE/TEMPERATURE CURVE = "E"
BETA "β" (0 TO +50°C) = 3,263°K NOMINAL
BETA "β" (+25 TO +85°C) = 3,347°K NOMINAL
TEMPERATURE COEFFICIENT @ +25°C = −3.67%/°C NOMINAL
DISSIPATION CONSTANT = 2 mW/°C NOMINAL
THERMAL TIME CONSTANT = 8 SECONDS NOMINAL
MAXIMUM TEMPERATURE RATING = +220°C

PACKAGING: BULK

SEE MANUFACTURING SPECIFICATION (LAYER 1)

REV	REVISION RECORD	DATE	APP
NONE	RELEASE TO PRODUCTION	10/23/15	DD

SCALE NONE	U.S. SENSOR CORP.
DRAWN BY DAN DANKERT	© COPYRIGHT
DATE 10/23/15	714-639-1000 www.ussensor.com
REV. NONE	NTC THERMISTOR
LAYER 0 OF 2	P/N SM102E1K

Downloaded from Arrow.com.