

Part Number : [194190014](#)

Product Description : MX150L 10 Circuit Plug for 16-14 AWG Wire

Series Number : 19419

Status : Active

Product Category : Connector Housings



Documents & Resources

Drawings

[194190014_sd.pdf](#)

[PK-19419-001-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-19417-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	19419
Description	MX150L 10 Circuit Plug for 16-14 AWG Wire
Application	Power, Wire-to-Wire
Comments	IP67 rated; Conforms to UL 1977; NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)
Product Name	MX150L
UPC	822348020027

Agency

CSA	LR18689
UL	E152602

Physical

Circuits (maximum)	10
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No

Lock to Mating Part	Yes
Net Weight	21.965/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
MX150L Receptacle Housings	<u>19418</u>

Use with Part(s)

Description	Part Number
MX150L Male Terminals and Circuit Voiding Keys	<u>19417</u>

This document was generated on Sep 22, 2025