

Date	SYM	REVISION RECORD	AUTH	DR.	CK.
01/15/19	H	Updated Tolerances	T. B.	B.S.	
10/18/19	J	Added Weight of the part	T. B.	B.S.	





PCB LAYOUT

Weight: 0.77g

CELL SIZE	RETAINS BATTERY NUMBERS
20mm	BR2032, CR2032, DL2032, LIR 2032, BR2025, CR2025, DL2025, LIR 2025

SPECIFICATIONS:

* 0.25mm Phosphor Bronze ½H, Nickel plated
* Temperature Range: -40°C to +260°C
* Vibration test: 10-50-10 hz sweeped in 60 seconds
  x,y,z direction: 1 hour each direction
* Result: no dislodgement of the cell or damage
  no discontinuity over 10 micro-seconds
* Shock test: half sine wave acceleration 150g.
  6 m/s 3 shock pulses each direction per axis,
  total of 18 pulses
* Result: no evidence of physical damage
* ROHS COMPLIANT

Tolerance (Except as noted)	MPD Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735		
decimal ±.5 (.020)		Scale	Drawn By B.S. Approved By T.B.
Fractional ± .8 (.030)	Title: CR2032 BATTERY RETAINER, SMD		
Angular ± 3°	Date: 10/18/19	Drawing Number: BK-912	

Downloaded from Arrow.com.