




TAOGLAS®



Datasheet

LAN Transformer 1G Base-T PoE

Part No:
TM82467NL

Description:

1G Base-T transformer
Single Port and 24pin SMT with PoE

Features:

PoE (350mA) Compliant with IEEE 802.3af standard
CMC + Transformer + CMC
RoHS Compliant

1. Introduction	3
2. Specifications	4
3. Mechanical	5
4. Electrical	6
5. Packaging	7
Changelog	8

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.



1. Introduction



Featuring a compatible footprint with industry LAN transformers, and designed to work in demanding industrial environmental conditions, the Taoglas TM82467NL is a LAN Transformer 1GBase-T Single Port of 24pins that is capable for PoE (350mA).

Typical applications for this cost-effective part are:

- Industrial Automation
- Hubs
- Routers
- Switches
- Wireless Access Points

The Taoglas Magnetics Product Team have over fifteen years of LAN magnetics design and high-quality manufacturing. With an ever-expanding portfolio, we provide trusted products and services to customers within a wide range of applications such as: Networking and Interconnect Devices, Servers, Switches, Router, Communication systems and any Digital Consumer electronics.

The Taoglas Exos Series offer an extensive product line of LAN Transformers designed for commercial and industrial grade applications, supporting 10/100 Base-T (Exos100 Series), 1G Base-T (Exos1G Series) and 10G Base-T (Exos10G Series). These products include Single, Dual, and Quad configurations not only for standard applications but also for Power over Ethernet (PoE, PoE+, PoE++).

For more information on the range of products or for assistance with integration, contact your regional Taoglas customer support team.

2. Specifications

Electrical Performance @25°C	
Inductance OCL	350μH MIN @ 100KHz 0.2V 8mA
Turns Ratio (±5%)	1CT: 1CT
Insertion Loss	1-100MHz: -1.0dB Max
Return Loss (@Load 100Ω)	1-30MHz: -18dB Min
	40MHz: -14.4dB Min
	50MHz: -13.1dB Min
	60-80MHz: -12dB Min
	100MHz: -10dB Min
Cross talk	30MHz: -45dB Min
	60MHz: -40dB Min
	100MHz: -35dB Min
DCMR	30MHz: -40dB Min
	60MHz: -35dB Min
	100MHz: -30dB Min
Hi-Pot	1500Vrms Min


Environmental Specifications	
Operating Temperature	0°C TO +70°C

Compliance	
RoHS Compliant	

Storage requirements	
Humidity	MSL - 1
Storage Temperature	-40°C TO +85°C

3. Mechanical


3.1 Mechanical Drawings



Mechanical Specifications	
Length	15.1 mm
Width	10 mm
Height	8.2 mm
Mounting Style	Surface Mount (SMT)

Dimensions are in millimeters with the following tolerances: X.XX = ± 0.25

3.2 Pad Layout




Suggested pad layout


Dimensions are in millimeters with the following tolerances: X.XX = ± 0.10

4. Electrical

4.1 Electrical Drawings



4.2 Profile of Reflow Solder



Preheat :
Temperature (Ta-Tb):150-200°C
Time(T1-T2):60-180s

Holding Temperature:217°C
Time (TL):60-150s

Max Temperature (Tp):250(+0/-5°C)
Max Time (Tp):30Sec±10Sec

The average speed:3°C/S Max
The average cooling speed:6°C/S Max

From 25°C to Products out of the furnace:6 minutes Max

5. Packaging

5.1 SPQ


1 reel = 400 pcs

A (Carrier Tape Width): 32 ± 0.3 mm

B (Sprocket hole to Cavity center): 14.2 ± 0.2 mm

C (Cavity width): 16 ± 0.2 mm

Weight: 2.2kg



1 Carton = 6 reels = 2400 pcs

Carton dimensions: 580*355*235 mm

Carton Weight: 14.4 kg



5.2 Label

Taoglas Limited	
P/N NO: XXXXXXXX	
QYT: XXX PCS	DC: XXXX
DATE: XXXX-XX-XX	

SPQ Label (8x4cm)

Taoglas Limited	
P/N NO: XXXXXXXX	
PO: XXXXXXXX	B/N: XXXXXXXX
QYT: XXX PCS	DC: XXXX
DATE: XXXX-XX-XX	

Carton Label (8x4cm)

Changelog

Changelog for the datasheet

SPE-23-8-168 – TM82467NL

Revision: A (Original First Release)	
Date:	2023-07-01
Notes:	
Author:	Javier Vasena

Previous Revisions



www.taoglas.com

