





PRODUCT NUMBER	PITCH
NCxx71x100J0G	5.00 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW



Material:

- Item①Male contact pin: Copper Tin plated
- Item②Terminal(housing): Thermoplastic (UL94V-0)

Electrical:

- Voltage rating: 300V
- Current rating: 8A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus

N = Number of poles

Dim A=Nx5.0+3.2

Dim B=Nx5.0+0.7

Dim C=(N-1)x5.0

poles	Dim A	Dim B	Dim C
2-6p	±0.20	+0.15 -0	±0.20
6-12p	±0.30	+0.3 -0	±0.30
12-24p	±0.40	+0.4 -0	±0.40

PART NO.: NC xx 7 1 x 1 00J0 G

Solid block

No. of poles

02 2 poles

03 3 poles

... ..

24 24 poles

Color

0 Black (RAL9005)

2 Red (RAL3001/D)

3 Orange(RAL2011/P)

4 Yellow(RAL1018/A)

5 Green(RAL6018/T)

6 Blue (RAL5015/A)

8 Grey(RAL7035/D)

9 White(RAL1102)

C Green(RAL6018/U)

 RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family		
ltr	ecn no	dr	date		tolerances unless otherwise specified		TERMINAL BLOCK		
				angles	X.±0.5	MM	title		
				dr	X.X±0.3		TERMINAL BLOCK		
				enr	X.XX±0.1	scale	PLUGGABLE SOCKET,RIGHT ANGLE		
				chr			dwg no		
				appd			sheet 1 of 1		
							size		
							A4		
							type		
							CUSTOMER Drawing		
sheet index	revision	A							
	sheet	1							