

DFCH31G84HDJAA

Part Number/Tape & Reel information


Part Number	Packaging	MOQ
DFCH31G84HDJAA-RD1	330 mm dia. reel	1000 pcs/reel

Specifications -35 to +85°C

Parameter	IN→OUT
Center Frequency	F0 : 1842.5 MHz
Band Width (BW)	F0 ± 37.5 MHz
Insertion Loss	2.0 dB max.
Ripple at BW	0.8 dB max.
V.S.W.R. at BW	2.0 max.
Input Power	1.0 W max.
Attenuation Absolute value	F0±80MHz 8 dB min. F0-160MHz 30 dB min. F0+160MHz 26 dB min. F0±350MHz 30 dB min
Characteristic Impedance	50Ω

Frequency Response

S11 logMAG 5dB/REF0dB
S21 logMAG 10dB/REF0dB




All Rights Reserved, Copyright© Murata Manufacturing Co., Ltd

*Note: All the technical data and information contained herein are subject to change without advanced notice.

DFCH31G84HDJAA


Dimensions and Marking



NOTE : Construction of Number

LOT NO : 5N 5 : Year

N: Month (1 to 9, Oct.-O, Nov.-N, Dec.-D)

Recommend Land Pattern (reference)Electrode

Solder Resist


Note : Impedance of signal lines should be 50 ohms including land pattern. This standard condition is applying to the glass epoxy board (t = 1.0mm, dielectric constant = 4.8, copper plating on both surfaces) and the land patterns are connected to 50 ohms micro-strip lines on back side surface through the via hole.

All Rights Reserved, Copyright© Murata Manufacturing Co., Ltd

*Note: All the technical data and information contained herein are subject to change without advanced notice.


DFCH31G84HDJAA

Dimensions of Carrier Tape



TOLERANCES UNLESS
 OTHERWISE SPECIFIED : +/-0.1
 DIMENSIONS : mm

Dimensions of Reel




Murata Part Number	A+/-2.0	B+/-0.5	C+/-0.8	D+/-0.5	N (min.)	W1+/-1.5	W2 (max.)
DFCH31G84HDJAA-RD1	φ 330	φ 13	φ 21	2	φ 50	17.5	23

All Rights Reserved, Copyright© Murata Manufacturing Co., Ltd

*Note: All the technical data and information contained herein are subject to change without advanced notice.


DFCH31G84HDJAA

Taping Condition



DFCH31G84HDJAA

Reflow Soldering Standard Conditions




Measuring point of temperature : IN-OUT Terminals of The Device

Reflow Soldering : Both Convection and Infrared Rays, Hot Air and Hot Plate

		TP0 (°C)	TP1 (°C)	T1 (s)	TP2 (°C)	T2 (s)	TP3 (°C)
Reflow standard condition	Sn-40Pb solder	225+/-5	200	20 to 40	---	---	140 to 160
	Sn-3Ag-0.5Cu solder	245+/-5	220	30 to 60	---	---	150 to 180
Test condition of reflow heat resistance		260+5/-0	240	20	220	70	150 to 180

Allowable Temperature and Time of Reflow Soldering



All Rights Reserved, Copyright© Murata Manufacturing Co., Ltd

*Note: All the technical data and information contained herein are subject to change without advanced notice.