

Johanson Part Number 0850BM14E0016001T

Johanson Part Number: 0850BM14E0016001T

Johanson Company: JTI

Legacy P/N: 0850BM14E0016T

Size for Capacitors (EIA): None

Description: RF Match Bal, 0603,
770-860/860-928MHz, 2W, 1.3/2.2dB, Ni/Sn (RoHS),
Matched Balun + LPF integrated Passive Component
for Texas Instruments, 7" Reel Paper Tape

Specification Number: None

Life Cycle Stage: Active

NCNR: No

AEC Q200 Qualified: No

Thickness (Max): 0.028

Schedule B: 8534.00.00.85

Thickness (Min): 0.020

ITAR: No

End Band(Min): 0.00

ECCN: EAR99

End Band (max): 0.012

RoHS Compliance: Yes, RoHS 10/10

Standard Item: Yes

REACH: Yes

Lead Time Typical (Weeks)*: 16

Country of Origin: TW

Length (Min): 0.059

Product Family: Integrated Passive Components

Length (Max): 0.067

Product Subfamily: RF Matched Baluns

Width (Min): 0.027

Capacitance Value: None

Width (Max): 0.035

Cap Unit of Meas: None

Part Weight (mg): 48.55

Tolerance: None

Packaged Width (lb) Arm: None

Voltage: None

Packaging: 7" Reel Paper Tape

Dielectric Temp Coefficient: None

Packaging Qty: 4000

Termination: 0

Operating Temp Range: -40°C to +85°C

Marking: Special

Storage Temp Range (Packaged): -65°C to +125°C

Product Release Date: Aug. 17, 2016, 7 a.m.

Storage Temp Range (None Operating): +5°C to
+40°C with RH 20% to 70%

Harmonization: 8534.00.00.85

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: <https://johansontechnology.com/chipset-specific>

Printed from: <https://www.johansontechnology.com/part/0850BM14E0016001T/>