

# M12 Power IDC female L-code/d



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 296 2505
Specification	M12 Power IDC female L-code/d
HARTING eCatalogue	<a href="https://harting.com/21032962505">https://harting.com/21032962505</a>

## Identification

Category	Connectors
Series	Circular connectors M12
Identification	Power
Element	Cable connector
Specification	Straight

## Version

Termination method	HARAX <sup>®</sup> connection technology
Gender	Female
Shielding	Shielded
Number of contacts	5
Number of power contacts	4
Number of special contacts	1
Specification of special contacts	FE contact
Coding	L-coding
Locking type	Screw locking

## Technical characteristics

Conductor cross-section	0.75 ... 1.5 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 18 ... AWG 16
Rated current	12 A
Rated voltage	63 V
Rated impulse voltage	1.5 kV



**Pushing Performance**  
Since 1945

## Technical characteristics

Pollution degree	3
Overvoltage category	III
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Tightening torque	0.6 Nm
Wrench size (knurled screw / knurled nut)	17
Limiting temperature	-40 ... +85 °C
Mating cycles	$\geq 100$
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	5.8 ... 13.5 mm
Isolation group	I ( $600 \leq \text{CTI}$ )

## Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Grey
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 61076-2-111
UL / CSA	UL 2238 CYJV2.E302521 CSA-C22.2 No. 182.3 CYJV8.E302521



**Pushing Performance**  
Since 1945

Specifications and approvals

PROFINET	Yes
----------	-----

Commercial data

Packaging size	1
Net weight	60 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140227255
eCl@ss	27440116 Circular connector (for field assembly)
ETIM	EC002635
UNSPSC 24.0	39121413