

1/4" PASS-THRU
EXAMPLE CONFIGURATION & OPTIONS

TABLE A: PASS-THRU OPTIONS

PART NUMBER	DESCRIPTION	COLOR	STUD THREAD	STUD LENGTH
PTB-14D-10	PASS THRU - 1/4-28 WITH NYLON LOCKNUT - BLACK	BLACK	1/4"-28	0.50"
PTR-14D-10	PASS THRU - 1/4-28 WITH NYLON LOCKNUT - RED	RED	1/4"-28	0.50"

TABLE B: O-RING OPTIONS

PART NUMBER	DESCRIPTION	COLOR
SCI3-2000A-B001	O-RING - 022, FKM/VITON, SHORE 75A, BLACK	BLACK


TABLE C: STUD NUT OPTIONS

PART NUMBER	DESCRIPTION	TYPE	MATERIAL	MAX PANEL THICKNESS
C02-1035	1/4"-28 SERRATED FLANGE NUT	FLANGE NUT	ZINC PLATED STEEL	0.36"


EXAMPLE
O-RING



EXAMPLE 1/4"
PASS-THRU




EXAMPLE
SERRATED FLANGE NUT



EXAMPLE CONFIGURATION
EXPLODE VIEW

TYPICAL PANEL CUTOUT



- NOTES:
- SEE COMPONENT PART NUMBER DRAWINGS FOR ADDITIONAL DIMENSIONS & DETAILS.
DIMENSIONS ARE FOR REFERENCE ONLY.
 - ALL PARTS SOLD INDIVIDUALLY AT QTY 1
 - AMPERAGE: UP TO 300A, DEPENDING ON WIRE GAUGE/BUSBAR
 - MAX TORQUE: 1/4"-28 STUD NUTS - 13Nm (10 FT-LBS)
BODY MOUNTING NUT - 16Nm (12 FT-LBS)
 - PROPER TORQUE VALUES FOR EACH APPLICATION MUST BE
DETERMINED BY CUSTOMER & NOT TO EXCEED MAXIMUM LISTED.
 - RoHS AND REACH COMPLIANT

EXAMPLE CONFIGURATION BOM

ITEM	DESCRIPTION	PART NO.	QTY
1	PASS THRU - 1/4-28 WITH NYLON LOCKNUT - RED	PTR-14D-10	1
2	O-RING - 022, FKM/VITON, SHORE 75A, BLACK	SCI3-2000A-B001	1
3	NUT - 1/4IN-28 ZINC PLATED STEEL - FLANGE NUT	C02-1035	2

GEP POWER PRODUCTS		16830 Pheasant Drive Brookfield, WI 53005		
PART NO:		PASS-THRU SERIES (SALES)		
DESCRIPTION:		PASS-THRU SERIES		
CUSTOMER:		STANDARD		
ENGLISH (IN)	REV 1	SHEET 2 OF 6	SCALE 1:1	SIZE B