




Home➤ Products > MICRO SWITCH™ Toggle Switches> TL > Product Page

▼ Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

4TL5-3D



Actual product appearance may vary.

TL Series Toggle Switch, 4 pole, 2 position, Screw terminal, Locking Lever

Features

Environmentproof sealing
1,2, and 4 pole circuitry
Standard and pull-to-unlock levers
2 and 3 position, maintained and momentary toggle action
Temperature range: -85° F to +160° F
Completely sealed switching chamber
Step-design case provides added space between terminals to help prevent shorting
UL recognized, CSA certified
CE approved

Description

MICRO SWITCH™TL Series toggle switches have high strength, temperature resistant, non-tracking case material and silver cadmium oxide contacts. Pull-to-Unlock toggle levers prevent accidental operation; the lever must be pulled approx. 2,3 mm (0.09 inches) to change positions.

Potential Applications

Industrial machinery and equipment
Military and commercial aviation
Construction equipment
Test instruments
Agricultural machinery
Process control
Medical instrumentation

Supporting Documentation

- ▶ Accessory: Seals
- ▶ Accessory: Nuts
- ▶ Engineering Drawing

Product Specifications	
Circuitry/Operating action	Keyway Position Opposite Keyway Position
Product Type	MICRO SWITCH™ Toggle Switch
Lever Lock	 Locked out of center position
Ampere/Voltage Range (Resistive Load)	0.75 A at 115 Vdc,0.5 A at 250 Vdc,0.5 A to 20 A at 0.5 Vdc to 28 Vdc,0.5 A to 15 A at 0.5 Vac to 277 Vac
Circuitry	4PDT
Action	2 position
Mounting	Bushing 15/32 in
Termination	Screw
Lever Type	Locking
UL/CSA Rating Code	L191: 15 A - 125, 250, 277 Vac; 1/2 Hp - 125 Vac; 1 Hp - 250, 277 Vac; 5 A - 120 Vac "L"
Comment	Bright nickel plated lever
Availability	Global
UNSPSC Code	30211908
UNSPSC Commodity	30211908 Toggle switches
Series Name	TL

Keyword Search

Search for product and support information.

All Sensing and Control▼

Product Search

Part number search:

Use (*) to expand search

Specification Search