Part Number : 1300390341
Product Description : Mini-Change 5 Pole Tee Adapter, DeviceNet Female to Male
Series Number : 130039
Status : Active
Product Category : Industrial Tees and Splitters
Engineering Part Number : DND3020



Documents and Resources

Drawings

1300390341_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025) SCIP:a7e0fa2d-e487-4282-85ae-156da09436eb
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	130039
Description	Mini-Change 5 Pole Tee Adapter, DeviceNet Female to Male
IP Rating	IP67
Product Name	DeviceNet Trunk,Mini-Change,Micro-Change (M12)
Type	Drop Tee
UPC	78678849469

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Color - Cable Jacket	Gray
Drop Connector	Micro-Change (M12)
Drop Gender	Female
Keyway	Single
LED Indicator	None
Left Trunk Connector	Mini-Change
Left Trunk Gender	Female
Leg 1 Length	N/A

Downloaded from Arrow.com.

Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	Nylon, TPE
Material - Coupling Nut	Zinc Die-Cast
Net Weight	65.650/g
Poles	5
Right Trunk Connector	Mini-Change
Right Trunk Gender	Male
Temperature Range - Operating	-20° to +80°C

Downloaded from Arrow.com.