Part Number : 1200698697
Product Description : Micro-Change (M12) Double-Ended Cordset with Knurled Hexnut, 5 Poles, A-Coded, Male (Straight) to Female (90°), 22 AWG, Black TPU WSOR Cable, 5.0m (16.40') Length
Series Number : 120069
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 885S31BS1M050



Documents and Resources

Drawings

1200698697_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	120069
Description	Micro-Change (M12) Double-Ended Cordset with Knurled Hexnut, 5 Poles, A-Coded, Male (Straight) to Female (90°), 22 AWG, Black TPU WSOR Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	889056132183

Agency

UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Physical

Cable Diameter	6.10mm (.240")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Male

Downloaded from Arrow.com.

Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	311.500/g
Orientation	90° to Straight
Poles	5
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	22

Downloaded from Arrow.com.