

| PART NUMBER | MADE FROM | MEAN SURFACE AREA SQ. IN. |
|----------------|---------------|---------------------------|
| 10-130028- 8() | 10-130028- 8C | |
| -10() | -10C | |
| -12() | -12C | |
| -13() | -13C | |
| -14() | -14C | |
| -15() | -15C | |
| -16() | -16C | |
| -17() | -17C | |
| -18() | -18C | |
| -20() | -20C | |
| -22() | -22C | |
| -24() | -24C | |
| -28() | -28C | |
| -32() | -32C | |
| -36() | -36C | |
| -40() | -40C | |
| -44() | -44C | |



| 31508-294 | | REVISIONS | |
|-----------|--|----------------------|----------------------|
| LTR | DESCRIPTION | DATE | APPROVED |
| A2 | REDRAWN, SAME SIZE, STANDARDIZED, ADDED -XXG & DATA ECN: 55525-109 | 10-9-73 R. GOULD | <i>R. Gould</i> |
| B | (MFG) ADD & REL -XX8 & DATA (NOTE 1) ECN: 58500-81 | 8-2-76 BARTKOW | <i>Bartkow</i> BT |
| C | (CL II) ADD & REL -XX9 & DATA ECN: 74500-209 | 7-14-83 FRESCOTT | <i>Frescott</i> |
| D | (CL II) ADD & REL -XXY & DATA ECN: 80699 | 9-13-95 DEMATTEO | <i>DeMatteo</i> |
| E | (CL II) ADD & REL -XXU & DATA ECN: 81117 | 12-20-95 DEMATTEO | <i>DeMatteo</i> |
| F | (CL I) REMOVED IN NOTE 1 "GREY ANODIZE SUFFIX -XX4 9-2671" / CHG'D BENDIX TO AMPHENOL ECN: A9225 | 4-13-11 JONES | |

- FOR RELEASE STATUS OF DESIRED PART, SEE SEPARATE PARTS LIST.
- THREADS ARE CLASS 2B AND TO BE IN ACCORDANCE WITH FEDERAL STANDARDS HANDBOOK H-28.
- TO COMPLETE PART NUMBER, ADD APPLICABLE LAST CHARACTER SUFFIX FOR DESIRED FINISH:

CHROMATE TREAT
BRIGHT CADMIUM PLATE
BLACK ANODIZE
OLIVE DRAB CADMIUM PLATE

NICKEL ALLOY PLATE
BRIGHT NICKEL
OLIVE DRAB CADMIUM PLATE,
NICKEL BASE PLATE

BLACK ZINC ALLOY PLATE

NOTES: OLIVE-GREEN ZINC ALLOY PLATE SUFFIX-XXU
9-9263

| SUFFIX | | |
|--------|--------|--|
| -XX0 | 9-3350 | |
| -XX1 | 9-2158 | |
| -XX2 | 9-2505 | |
| -XX3 | 9-3047 | |
| -XXG | 9-6914 | |
| -XX8 | 9-3435 | |
| -XX9 | 9-4960 | |
| -XXY | 9-9181 | |

10-131008/50 & OTHERS
NEXT ASSEMBLY

| FIND NO. | QTY REQD | CODE IDENT | PART NUMBER | DESCRIPTION | NOTE REF |
|---|----------|---|-------------|---|----------|
| PARTS LIST | | | | | |
| USE OF THIS DOCUMENT IS UNLIMITED. DOCUMENTS REFERENCED HEREON CONTAIN LIMITED RIGHTS DATA. | | | | | |
| UNLESS OTHERWISE SPECIFIED LINEAR DIMENSIONS ARE IN INCHES TOLERANCES: .XXX ± .010 .XX ± .03 .X ± .1 ANGLES ± 2° OTHER STANDARDS PER 9-3800 AND MIL-D-1000. NOTE REF ◁ | | SIGNATURES PREPARED POMPEII CHECKED <i>S.M. Miller</i> APPROVED <i>E. Shepley</i> APPROVED <i>2/21/73</i> | | DATES 9-6-56 12-11-73 10-16-73 12-12-73 | |
| MATERIAL SPEC | | MATERIAL | | AMPHENOL CORPORATION 40-60 DELAWARE AVENUE SIDNEY, NEW YORK | |
| PROCESS SPEC SEE NOTE 1 | | APPROVED <i>2/21/73</i> | | NUT, GROMMET RETAINING, ELECTRICAL CONNECTOR | |
| | | SIZE B | | CODE IDENT NO. 77820 | |
| | | SCALE NONE | | 10-130028 | |
| | | WGT SEE PL | | REF | |
| | | | | SHEET | |