



**Part Number :** [1300390341](#)

**Product Description :** Mini-Change 5 Pole Tee Adapter, DeviceNet Female to Male

**Series Number :** 130039

**Status :** Active

**Product Category :** Industrial Tees and Splitters

**Engineering Part Number :** DND3020



---

## Documents and Resources


### Drawings

[1300390341\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025) SCIP:a7e0fa2d-e487-4282-85ae-156da09436eb
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

## Part Details

### General

Status	Active
Category	Industrial Tees and Splitters
Series	130039
Description	Mini-Change 5 Pole Tee Adapter, DeviceNet Female to Male
IP Rating	IP67
Product Name	DeviceNet Trunk
Type	Drop Tee
UPC	78678849469

### Agency

CSA	LR6837
UL	E152210

### Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

### Physical

Color - Cable Jacket	Gray
Drop Connector	Micro-Change (M12)
Drop Gender	Female
Keyway	Single
LED Indicator	None
Left Trunk Connector	Mini-Change

Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	Nylon, TPE
Material - Coupling Nut	Zinc Die-Cast
Net Weight	65.650/g
Poles	5
Right Trunk Connector	Mini-Change
Right Trunk Gender	Male
Temperature Range - Operating	-20° to +80°C

---

This document was generated on May 26, 2026