



Part Number: D4C2004


Electrical Specifications

Frequency Range (GHz):	20.0 – 40.0
Isolation (dB):	10 MIN (per junction)
Insertion Loss (dB):	2.0 MAX (per junction)
VSWR:	2.0:1 MIN
Forward Power (W):	2 AVG
	30 PK


Mechanical/Environmental Specifications

Connector Type:	K (2.92mm)
Connector Body:	Passivated stainless steel
Connector Pin:	Gold plated copper
Load Body:	Brass
Magnetic Shunt:	Nickel plated CRS
Operational Temp:	-20°C to +65°C
Weight (oz)	2.0 MAX

D4C2004 Dimensions



D4C2004-3 Dimensions



Type of Device	PN Suffix	Connector Configuration Input / Output	PN Example
Dual Junction Circulator 4-Port Device Port 1 / Port 2 / Port 3 / Port 4	No Dash	Female / Female / Female / Female	D4C2004
	-1	Male / Female / Female / Female	D4C2004-1
	-2	Female / Male / Female / Female	D4C2004-2
	-3	Male / Male / Male / Male	D4C2004-3
	-4	Female / Female / Male / Female	D4C2004-4
	-5	Female / Female / Female / Male	D4C2004-5



MEASURED DATA

Part Number: D4C2004, P4→P1, P2 & P3 Terminated with 50Ω, +25°C

