







Customer Drawing



DIMENSION TABLE						
SHELL SIZE	POSITIONS	A	B	C	E	F
E	09	30.81	24.99	16.92	11.08	19.20
A	15	39.14	33.32	25.25	19.39	27.70
B	25	53.04	47.04	38.96	33.24	41.10
C	37	69.32	63.50	55.42	49.86	57.30




REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1	HK--	First Release Drawing	Aug/02/11	IP
2	HK--	Add dimension 5.9"	10/20/16	IP
3	HK--	Add dimension 4.50	05/24/19	IP
4	HK--	Add terminal dimension	05/06/23	Tony,Tang

D-SUB TECHNICAL DATA

- SHELL : Steel, 100u" min tin plated over 50u" min nickel over 50u" min Copper
- BODY : PBT UL 94V-0 Color: Black
- CONTACTS : Copper Alloy
- Gold flash over 50u" min nickel on mating area.
- 100u" min tin over 50u" min nickel on solder area.
- CLINCH NUT: Copper alloy, 30u" min Nickel plated.
- ELECTRICAL : Voltage rating 250 V Rms
- Current rating 3A.
- Withstanding Voltage >1000 V Rms
- Insulation resistance >1000 M Ohms
- Contact resistance 20 mOhms max.
- MARKING : Amphenol...(Series No.)
- Commercial reference
- Manufacturing date

PRODUCT CODE

L 717 SD X H XX P 012



DIMENSIONS OTHERWISE SPECIFIED		APPROVAL DATE	
TOLERANCES	D.S.	DRAWN	DATE
ASSEMBLY	0.50	BALDI, P.	06/06/23
FINISHES	0.30	CHECKED	FRONG, TONG
ANGLES	0.20		06/06/23
FOR MATERIALS AND FINISHES	SEE NOTES		
REMOVE SHARP EDGES			
DIMENSIONS	INCHES		
TERMINAL	MM		
ANGLE OF PROJECTION			
SIZE	DRAWING NO.	REV.	
A4	L717SDXHXXP012	4	
SCALE	NONE	SHEET	1 OF 1

Amphenol

D-SUB connector, SD Series