

# Single D Flip Flop

## NL17SZ74

The NL17SZ74 is a high performance, full function Edge triggered D Flip Flop, with all the features of a standard logic device such as the 74LCX74.

### Features

- Designed for 1.65 V to 5.5 V  $V_{CC}$  Operation
- 2.6 ns  $t_{PD}$  at  $V_{CC} = 5$  V (typ)
- Inputs/Outputs Overvoltage Tolerant up to 5.5 V
- $I_{OFF}$  Supports Partial Power Down Protection
- Source/Sink 24 mA at 3.0 V
- Available in US8, UDFN8 and UQFN8 Packages
- Chip Complexity < 100 FETs
- NLV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant




Figure 1. Logic Symbol




ON Semiconductor®

[www.onsemi.com](http://www.onsemi.com)


### MARKING DIAGRAMS




US8  
US SUFFIX  
CASE 493




UDFN8, 1.45x1.0  
MU3 SUFFIX  
CASE 517BZ




UDFN8, 1.95x1.0  
MU1 SUFFIX  
CASE 517CA



UQFN8, 1.4x1.2  
MQ2 SUFFIX  
CASE 523AS



UQFN8, 1.6x1.6  
MQ1 SUFFIX  
CASE 523AN



X, XX, XXXX = Specific Device Code  
A = Assembly Location  
L = Lot Code  
Y = Year Code  
W = Week Code  
M = Date Code  
▪ = Pb-Free Package

### ORDERING INFORMATION

See detailed ordering, marking and shipping information in the package dimensions section on page 8 of this data sheet.

# NL17SZ74




Figure 2. Pinout (Top View)

## PIN ASSIGNMENT

| Pin | US8             | UDFN8           | UQFN8, 1.4x1.2  | UQFN8, 1.6x1.6  |
|-----|-----------------|-----------------|-----------------|-----------------|
| 1   | CP              | CP              | V <sub>CC</sub> | PR              |
| 2   | D               | D               | CP              | CLR             |
| 3   | Q               | Q               | D               | Q               |
| 4   | GND             | GND             | Q               | GND             |
| 5   | Q               | Q               | GND             | Q               |
| 6   | CLR             | CLR             | Q               | D               |
| 7   | PR              | PR              | CLR             | CP              |
| 8   | V <sub>CC</sub> | V <sub>CC</sub> | PR              | V <sub>CC</sub> |

## FUNCTION TABLE

| Inputs |     |    |   | Outputs |    | Operating Mode                                            |
|--------|-----|----|---|---------|----|-----------------------------------------------------------|
| PR     | CLR | CP | D | Q       | Q  |                                                           |
| L      | H   | X  | X | H       | L  | Asynchronous Set<br>Asynchronous Clear<br>Underdetermined |
| H      | L   | X  | X | L       | H  |                                                           |
| L      | L   | X  | X | H       | H  |                                                           |
| H      | H   | ↑  | h | H       | L  | Load and Read<br>Register                                 |
| H      | H   | ↑  | l | L       | H  |                                                           |
| H      | H   | ⊕  | X | NC      | NC | Hold                                                      |

H = High Voltage Level

h = High Voltage Level One Setup Time Prior to Low-to-High Clock Transition

L = Low Voltage Level

l = Low Voltage Level One Setup Time Prior to Low-to-High Clock Transition

NC = No Change

X = High or Low Voltage Level and Transitions are Acceptable

↑ = Low-to-High Transition

⊕ = Low-to-High Transition

For I<sub>CC</sub> reasons, DO NOT FLOAT Inputs

# MAXIMUM RATINGS

| Symbol                              | Characteristics                                                                                                               | Value                                                         | Unit |
|-------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------|------|
| V <sub>CC</sub>                     | DC Supply Voltage NLV                                                                                                         | –0.5 to +7.0<br>–0.5 to +6.5                                  | V    |
| V <sub>IN</sub>                     | DC Input Voltage NLV                                                                                                          | –0.5 to +7.0<br>–0.5 to +6.5                                  | V    |
| V <sub>OUT</sub>                    | DC Output Voltage (NLV) Active-Mode (High or Low State)<br>Tri-State Mode (Note 6)<br>Power-Down Mode (V <sub>CC</sub> = 0 V) | –0.5 to V <sub>CC</sub> + 0.5<br>–0.5 to +7.0<br>–0.5 to +7.0 | V    |
|                                     | DC Output Voltage Active-Mode (High or Low State)<br>Tri-State Mode (Note 6)<br>Power-Down Mode (V <sub>CC</sub> = 0 V)       | –0.5 to V <sub>CC</sub> + 0.5<br>–0.5 to +6.5<br>–0.5 to +6.5 | V    |
| I <sub>IK</sub>                     | DC Input Diode Current V <sub>IN</sub> < GND                                                                                  | –50                                                           | mA   |
| I <sub>OK</sub>                     | DC Output Diode Current V <sub>OUT</sub> < GND                                                                                | –50                                                           | mA   |
| I <sub>OUT</sub>                    | DC Output Source/Sink Current                                                                                                 | ±50                                                           | mA   |
| I <sub>CC</sub> or I <sub>GND</sub> | DC Supply Current per Supply Pin or Ground Pin                                                                                | ±100                                                          | mA   |
| T <sub>STG</sub>                    | Storage Temperature Range                                                                                                     | –65 to +150                                                   | °C   |
| T <sub>L</sub>                      | Lead Temperature, 1 mm from Case for 10 secs                                                                                  | 260                                                           | °C   |
| T <sub>J</sub>                      | Junction Temperature Under Bias                                                                                               | +150                                                          | °C   |
| θ <sub>JA</sub>                     | Thermal Resistance (Note 7) US8<br>UQFN8<br>UDFN8                                                                             | 250<br>210<br>231                                             | °C/W |
| P <sub>D</sub>                      | Power Dissipation in Still Air US8<br>UQFN8<br>UDFN8                                                                          | 500<br>595<br>541                                             | mW   |
| MSL                                 | Moisture Sensitivity                                                                                                          | Level 1                                                       | –    |
| F <sub>R</sub>                      | Flammability Rating Oxygen Index: 28 to 34                                                                                    | UL 94 V–0 @ 0.125 in                                          | –    |
| V <sub>ESD</sub>                    | ESD Withstand Voltage (Note 8) Human Body Model<br>Charged Device Model                                                       | 2000<br>1000                                                  | V    |
| I <sub>Latchup</sub>                | Latchup Performance (Note 9)                                                                                                  | ±100                                                          | mA   |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Applicable to devices with outputs that may be tri-stated.
2. Measured with minimum pad spacing on an FR4 board, using 10mm-by-1inch, 2 ounce copper trace no air flow per JESD51–7.
3. HBM tested to ANSI/ESDA/JEDEC JS–001–2017. CDM tested to EIA/JESD22–C101–F. JEDEC recommends that ESD qualification to EIA/JESD22–A115–A (Machine Model) be discontinued per JEDEC/JEP172A.
4. Tested to EIA/JESD78 Class II.

# RECOMMENDED OPERATING CONDITIONS

| Symbol           | Characteristics                                                                                                                                                         | Min              | Max                           | Unit |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|-------------------------------|------|
| V <sub>CC</sub>  | Positive DC Supply Voltage                                                                                                                                              | 1.65             | 5.5                           | V    |
| V <sub>IN</sub>  | DC Input Voltage                                                                                                                                                        | 0                | 5.5                           | V    |
| V <sub>OUT</sub> | DC Output Voltage Active-Mode (High or Low State)<br>Tri-State Mode (Note 6)<br>Power-Down Mode (V <sub>CC</sub> = 0 V)                                                 | 0<br>0<br>0      | V <sub>CC</sub><br>5.5<br>5.5 |      |
| T <sub>A</sub>   | Operating Temperature Range                                                                                                                                             | –55              | +125                          | °C   |
|                  | Input Rise and Fall Time V <sub>CC</sub> = 1.65 V to 1.95 V<br>V <sub>CC</sub> = 2.3 V to 2.7 V<br>V <sub>CC</sub> = 3.0 V to 3.6 V<br>V <sub>CC</sub> = 4.5 V to 5.5 V | 0<br>0<br>0<br>0 | 20<br>20<br>10<br>5           |      |

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

DC ELECTRICAL CHARACTERISTICS

| Symbol           | Parameter                 | Condition                                            | V <sub>CC</sub><br>(V) | T <sub>A</sub> = 25°C |                 |                      | -55°C ≤ T <sub>A</sub> ≤ 125°C |                      | Units |
|------------------|---------------------------|------------------------------------------------------|------------------------|-----------------------|-----------------|----------------------|--------------------------------|----------------------|-------|
|                  |                           |                                                      |                        | Min                   | Typ             | Max                  | Min                            | Max                  |       |
| V <sub>IH</sub>  | High-Level Input Voltage  |                                                      | 1.65 to 1.95           | 0.65 V <sub>CC</sub>  | –               | –                    | 0.65 V <sub>CC</sub>           | –                    | V     |
|                  |                           |                                                      | 2.3 to 5.5             | 0.70 V <sub>CC</sub>  | –               | –                    | 0.70 V <sub>CC</sub>           | –                    |       |
| V <sub>IL</sub>  | Low-Level Input Voltage   |                                                      | 1.65 to 1.95           | –                     | –               | 0.35 V <sub>CC</sub> | –                              | 0.35 V <sub>CC</sub> | V     |
|                  |                           |                                                      | 2.3 to 5.5             | –                     | –               | 0.30 V <sub>CC</sub> | –                              | 0.30 V <sub>CC</sub> |       |
| V <sub>OH</sub>  | High-Level Output Voltage | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub> | 1.65 to 5.5            | V <sub>CC</sub> – 0.1 | V <sub>CC</sub> | –                    | V <sub>CC</sub> – 0.1          | –                    | V     |
|                  |                           | I <sub>OH</sub> = –100 μA                            | 1.65                   | 1.29                  | 1.4             | –                    | 1.29                           | –                    |       |
|                  |                           | I <sub>OH</sub> = –4 mA                              | 2.3                    | 1.9                   | 2.1             | –                    | 1.9                            | –                    |       |
|                  |                           | I <sub>OH</sub> = –8 mA                              | 2.7                    | 2.2                   | 2.4             | –                    | 2.2                            | –                    |       |
|                  |                           | I <sub>OH</sub> = –12 mA                             | 3.0                    | 2.4                   | 2.7             | –                    | 2.4                            | –                    |       |
|                  |                           | I <sub>OH</sub> = –16 mA                             | 3.0                    | 2.3                   | 2.5             | –                    | 2.3                            | –                    |       |
|                  |                           | I <sub>OH</sub> = –24 mA                             | 4.5                    | 3.8                   | 4.0             | –                    | 3.8                            | –                    |       |
|                  |                           | I <sub>OH</sub> = –32 mA                             |                        |                       |                 |                      |                                |                      |       |
| V <sub>OL</sub>  | Low-Level Output Voltage  | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub> | 1.65 to 5.5            | –                     | –               | 0.1                  | –                              | 0.1                  | V     |
|                  |                           | I <sub>OL</sub> = 100 μA                             | 1.65                   | –                     | 0.08            | 0.24                 | –                              | 0.24                 |       |
|                  |                           | I <sub>OL</sub> = 4 mA                               | 2.3                    | –                     | 0.2             | 0.3                  | –                              | 0.3                  |       |
|                  |                           | I <sub>OL</sub> = 8 mA                               | 2.7                    | –                     | 0.22            | 0.4                  | –                              | 0.4                  |       |
|                  |                           | I <sub>OL</sub> = 12 mA                              | 3.0                    | –                     | 0.28            | 0.4                  | –                              | 0.4                  |       |
|                  |                           | I <sub>OL</sub> = 16 mA                              | 3.0                    | –                     | 0.38            | 0.55                 | –                              | 0.55                 |       |
|                  |                           | I <sub>OL</sub> = 24 mA                              | 4.5                    | –                     | 0.42            | 0.55                 | –                              | 0.55                 |       |
|                  |                           | I <sub>OL</sub> = 32 mA                              |                        |                       |                 |                      |                                |                      |       |
| I <sub>IN</sub>  | Input Leakage Current     | V <sub>IN</sub> = 5.5 V or GND                       | 1.65 to 5.5            | –                     | –               | ±0.1                 | –                              | ±1.0                 | μA    |
| I <sub>OFF</sub> | Power Off Leakage Current | V <sub>IN</sub> = 5.5 V or V <sub>OUT</sub> = 5.5 V  | 0                      | –                     | –               | 1.0                  | –                              | 10                   | μA    |
| I <sub>CC</sub>  | Quiescent Supply Current  | V <sub>IN</sub> = V <sub>CC</sub> or GND             | 5.5                    | –                     | –               | 1.0                  | –                              | 10                   | μA    |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

## AC ELECTRICAL CHARACTERISTICS


| Symbol                                 | Parameter                                                         | V <sub>CC</sub> (V) | Test Conditions                                                          | T <sub>A</sub> = 25°C |     |      | T <sub>A</sub> = -55 to 125°C |      | Units |
|----------------------------------------|-------------------------------------------------------------------|---------------------|--------------------------------------------------------------------------|-----------------------|-----|------|-------------------------------|------|-------|
|                                        |                                                                   |                     |                                                                          | Min                   | Typ | Max  | Min                           | Max  |       |
| f <sub>MAX</sub>                       | Maximum Clock Frequency<br>(50% Duty Cycle)<br>(Waveform 1)       | 1.65 to 1.95        | C <sub>L</sub> = 15 pF<br>R <sub>L</sub> = 1 MΩ<br>S <sub>1</sub> = Open | 75                    | –   | –    | 75                            | –    | MHz   |
|                                        |                                                                   | 2.3 to 2.7          |                                                                          | 150                   | –   | –    | 150                           | –    |       |
|                                        |                                                                   | 3.0 to 3.6          |                                                                          | 200                   | –   | –    | 200                           | –    |       |
|                                        |                                                                   | 4.5 to 5.5          |                                                                          | 250                   | –   | –    | 250                           | –    |       |
|                                        |                                                                   | 3.0 to 3.6          | C <sub>L</sub> = 50 pF,<br>R <sub>L</sub> = 500 Ω, S <sub>1</sub> = Open | 175                   | –   | –    | 175                           | –    |       |
|                                        |                                                                   | 4.5 to 5.5          |                                                                          | 200                   | –   | –    | 200                           | –    |       |
| t <sub>PLH</sub> ,<br>t <sub>PHL</sub> | Propagation Delay,<br>CP to Q or $\bar{Q}$<br>(Waveform 1)        | 1.65 to 1.95        | C <sub>L</sub> = 15 pF<br>R <sub>L</sub> = 1 MΩ<br>S <sub>1</sub> = Open | –                     | 6.5 | 12.5 | –                             | 13   | ns    |
|                                        |                                                                   | 2.3 to 2.7          |                                                                          | –                     | 3.8 | 7.5  | –                             | 8.0  |       |
|                                        |                                                                   | 3.0 to 3.6          |                                                                          | –                     | 2.8 | 6.5  | –                             | 7.0  |       |
|                                        |                                                                   | 4.5 to 5.5          |                                                                          | –                     | 2.2 | 4.5  | –                             | 5.0  |       |
|                                        |                                                                   | 3.0 to 3.6          | C <sub>L</sub> = 50 pF,<br>R <sub>D</sub> = 500 Ω, S <sub>1</sub> = Open | –                     | 3.4 | 7.0  | –                             | 7.5  |       |
|                                        |                                                                   | 4.5 to 5.5          |                                                                          | –                     | 2.6 | 5.0  | –                             | 5.5  |       |
| t <sub>PLH</sub> ,<br>t <sub>PHL</sub> | Propagation Delay,<br>PR or CLR to Q or $\bar{Q}$<br>(Waveform 2) | 1.65 to 1.95        | C <sub>L</sub> = 15 pF<br>R <sub>L</sub> = 1 MΩ<br>S <sub>1</sub> = Open | –                     | 6.5 | 14   | –                             | 14.5 | ns    |
|                                        |                                                                   | 2.3 to 2.7          |                                                                          | –                     | 3.8 | 9.0  | –                             | 9.5  |       |
|                                        |                                                                   | 3.0 to 3.6          |                                                                          | –                     | 2.8 | 6.5  | –                             | 7.0  |       |
|                                        |                                                                   | 4.5 to 5.5          |                                                                          | –                     | 2.2 | 5.0  | –                             | 5.5  |       |
|                                        |                                                                   | 3.0 to 3.6          | C <sub>L</sub> = 50 pF,<br>R <sub>L</sub> = 500 Ω, S <sub>1</sub> = Open | –                     | 3.4 | 7.0  | –                             | 7.5  |       |
|                                        |                                                                   | 4.5 to 5.5          |                                                                          | –                     | 2.6 | 5.0  | –                             | 5.5  |       |
| t <sub>S</sub>                         | Setup Time, D to CP<br>(Waveform 1)                               | 1.65 to 1.95        | C <sub>L</sub> = 15 pF<br>R <sub>L</sub> = 1 MΩ<br>S <sub>1</sub> = Open | 6.5                   | –   | –    | 6.5                           | –    | ns    |
|                                        |                                                                   | 2.3 to 2.7          |                                                                          | 3.5                   | –   | –    | 3.5                           | –    |       |
|                                        |                                                                   | 3.0 to 3.6          |                                                                          | 2.0                   | –   | –    | 2.0                           | –    |       |
|                                        |                                                                   | 4.5 to 5.5          |                                                                          | 1.5                   | –   | –    | 1.5                           | –    |       |
|                                        |                                                                   | 3.0 to 3.6          | C <sub>L</sub> = 50 pF,<br>R <sub>L</sub> = 500 Ω, S <sub>1</sub> = Open | 2.0                   | –   | –    | 2.0                           | –    |       |
|                                        |                                                                   | 4.5 to 5.5          |                                                                          | 1.5                   | –   | –    | 1.5                           | –    |       |
| t <sub>H</sub>                         | Hold Time, D to CP<br>(Waveform 1)                                | 1.65 to 1.95        | C <sub>L</sub> = 15 pF<br>R <sub>L</sub> = 1 MΩ<br>S <sub>1</sub> = Open | 0.5                   | –   | –    | 0.5                           | –    | ns    |
|                                        |                                                                   | 2.3 to 2.7          |                                                                          | 0.5                   | –   | –    | 0.5                           | –    |       |
|                                        |                                                                   | 3.0 to 3.6          |                                                                          | 0.5                   | –   | –    | 0.5                           | –    |       |
|                                        |                                                                   | 4.5 to 5.5          |                                                                          | 0.5                   | –   | –    | 0.5                           | –    |       |
|                                        |                                                                   | 3.0 to 3.6          | C <sub>L</sub> = 50 pF,<br>R <sub>L</sub> = 500 Ω, S <sub>1</sub> = Open | 0.5                   | –   | –    | 0.5                           | –    |       |
|                                        |                                                                   | 4.5 to 5.5          |                                                                          | 0.5                   | –   | –    | 0.5                           | –    |       |
| t <sub>W</sub>                         | Pulse Width,<br>CP, CLR, PR<br>(Waveform 3)                       | 1.65 to 1.95        | C <sub>L</sub> = 15 pF<br>R <sub>L</sub> = 1 MΩ<br>S <sub>1</sub> = Open | 6.0                   | –   | –    | 6.0                           | –    | ns    |
|                                        |                                                                   | 2.3 to 2.7          |                                                                          | 4.0                   | –   | –    | 4.0                           | –    |       |
|                                        |                                                                   | 3.0 to 3.6          |                                                                          | 3.0                   | –   | –    | 3.0                           | –    |       |
|                                        |                                                                   | 4.5 to 5.5          |                                                                          | 2.0                   | –   | –    | 2.0                           | –    |       |
|                                        |                                                                   | 3.0 to 3.6          | C <sub>L</sub> = 50 pF,<br>R <sub>L</sub> = 500 Ω, S <sub>1</sub> = Open | 3.0                   | –   | –    | 3.0                           | –    |       |
|                                        |                                                                   | 4.5 to 5.5          |                                                                          | 2.0                   | –   | –    | 2.0                           | –    |       |
| t <sub>REC</sub>                       | Recover Time<br>PR; CLR to CP<br>(Waveform 3)                     | 1.65 to 1.95        | C <sub>L</sub> = 15 pF<br>R <sub>D</sub> = 1 MΩ<br>S <sub>1</sub> = Open | 8.0                   | –   | –    | 8.0                           | –    | ns    |
|                                        |                                                                   | 2.3 to 2.7          |                                                                          | 4.5                   | –   | –    | 4.5                           | –    |       |
|                                        |                                                                   | 3.0 to 3.6          |                                                                          | 3.0                   | –   | –    | 3.0                           | –    |       |
|                                        |                                                                   | 4.5 to 5.5          |                                                                          | 3.0                   | –   | –    | 3.0                           | –    |       |
|                                        |                                                                   | 3.0 to 3.6          | C <sub>L</sub> = 50 pF,<br>R <sub>L</sub> = 500 Ω, S <sub>1</sub> = Open | 3.0                   | –   | –    | 3.0                           | –    |       |
|                                        |                                                                   | 4.5 to 5.5          |                                                                          | 3.0                   | –   | –    | 3.0                           | –    |       |

5. C<sub>PD</sub> is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load. Average operating current can be obtained by the equation: I<sub>CC(OPR)</sub> = C<sub>PD</sub> • V<sub>CC</sub> • f<sub>in</sub> + I<sub>CC</sub>/2 (per flip-flop). C<sub>PD</sub> is used to determine the no-load dynamic power consumption; P<sub>D</sub> = C<sub>PD</sub> • V<sub>CC</sub><sup>2</sup> • f<sub>in</sub> + I<sub>CC</sub> • V<sub>CC</sub>.

# CAPACITIVE CHARACTERISTICS

| Symbol    | Parameter                              | Condition                                                                                                                                      | Typical | Units |
|-----------|----------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------|---------|-------|
| $C_{IN}$  | Input Capacitance                      | $V_{CC} = 5.5 \text{ V}$ , $V_{IN} = 0 \text{ V}$ or $V_{CC}$                                                                                  | 2.5     | pF    |
| $C_{OUT}$ | Output Capacitance                     | $V_{CC} = 5.5 \text{ V}$ , $V_{IN} = 0 \text{ V}$ or $V_{CC}$                                                                                  | 2.5     | pF    |
| $C_{PD}$  | Power Dissipation Capacitance (Note 6) | 10 MHz, $V_{CC} = 3.3 \text{ V}$ , $V_{IN} = 0 \text{ V}$ or $V_{CC}$<br>10 MHz, $V_{CC} = 5.5 \text{ V}$ , $V_{IN} = 0 \text{ V}$ or $V_{CC}$ | 9<br>11 | pF    |

6.  $C_{PD}$  is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load. Average operating current can be obtained by the equation:  $I_{CC(OPR)} = C_{PD} \cdot V_{CC} \cdot f_{in} + I_{CC}$ .  $C_{PD}$  is used to determine the no-load dynamic power consumption;  $P_D = C_{PD} \cdot V_{CC}^2 \cdot f_{in} + I_{CC} \cdot V_{CC}$ .



$C_L$  includes probe and jig capacitance  
 $R_T$  is  $Z_{OUT}$  of pulse generator (typically 50  $\Omega$ )  
 $f = 1 \text{ MHz}$

Figure 3. Test Circuit

| Test                | Switch Position   | $C_L$ , pF                   | $R_L$ , $\Omega$ | $R_1$ , $\Omega$ |
|---------------------|-------------------|------------------------------|------------------|------------------|
| $t_{PLH} / t_{PHL}$ | Open              | See AC Characteristics Table |                  |                  |
| $t_{PLZ} / t_{PZL}$ | $2 \times V_{CC}$ | 50                           | 500              | 500              |
| $t_{PHZ} / t_{PZH}$ | GND               | 50                           | 500              | 500              |

X = Don't Care




Figure 4. Switching Waveforms

# NL17SZ74




Figure 5. Setup, Hold and Recovery Time Waveforms

| $V_{CC}, V$  | $V_{mi}, V$ | $V_{mo}, V$        |                                      | $V_Y, V$ |
|--------------|-------------|--------------------|--------------------------------------|----------|
|              |             | $t_{PLH}, t_{PHL}$ | $t_{PZL}, t_{PLZ}, t_{PZH}, t_{PHZ}$ |          |
| 1.65 to 1.95 | $V_{CC}/2$  | $V_{CC}/2$         | $V_{CC}/2$                           | 0.15     |
| 2.3 to 2.7   | $V_{CC}/2$  | $V_{CC}/2$         | $V_{CC}/2$                           | 0.15     |
| 3.0 to 3.6   | $V_{CC}/2$  | $V_{CC}/2$         | $V_{CC}/2$                           | 0.3      |
| 4.5 to 5.5   | $V_{CC}/2$  | $V_{CC}/2$         | $V_{CC}/2$                           | 0.3      |

# NL17SZ74


## DEVICE ORDERING INFORMATION

| Device                               | Packages                 | Marking | Pin 1 Orientation<br>(See below) | Shipping <sup>†</sup> |
|--------------------------------------|--------------------------|---------|----------------------------------|-----------------------|
| NL17SZ74USG                          | US8                      | MH      | Q4                               | 3000 / Tape & Reel    |
| NLV17SZ74USG*                        | US8                      | MH      | Q4                               | 3000 / Tape & Reel    |
| NL17SZ74MQ1TCG                       | UQFN8, 1.6 x 1.6, 0.5P   | AA      | Q1                               | 3000 / Tape & Reel    |
| NLV17SZ74MQ1TCG*<br>(In Development) | UQFN8, 1.6 x 1.6, 0.5P   | AA      | Q1                               | 3000 / Tape & Reel    |
| NL17SZ74MU1TCG<br>(In Development)   | UDFN8, 1.95 x 1.0, 0.5P  | TBD     | Q4                               | 3000 / Tape & Reel    |
| NL17SZ74MU3TCG<br>(In Development)   | UDFN8, 1.45 x 1.0, 0.35P | TBD     | Q4                               | 3000 / Tape & Reel    |
| NL17SZ74MQ2TCG<br>(In Development)   | UQFN8, 1.4 x 1.2, 0.4P   | TBD     | TBD                              | 3000 / Tape & Reel    |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

\*NLV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable.


### Pin 1 Orientation in Tape and Reel



# NL17SZ74

## PACKAGE DIMENSIONS

US8  
US SUFFIX  
CASE 493-02  
ISSUE B




### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION "A" DOES NOT INCLUDE MOLD FLASH, PROTRUSION OR GATE BURR. MOLD FLASH, PROTRUSION AND GATE BURR SHALL NOT EXCEED 0.140 MM (0.0055") PER SIDE.
4. DIMENSION "B" DOES NOT INCLUDE INTER-LEAD FLASH OR PROTRUSION. INTER-LEAD FLASH AND PROTRUSION SHALL NOT EXCEED 0.140 (0.0055") PER SIDE.
5. LEAD FINISH IS SOLDER PLATING WITH THICKNESS OF 0.0076-0.0203 MM. (300-800 °).
6. ALL TOLERANCE UNLESS OTHERWISE SPECIFIED ±0.0508 (0.0002 °).

| DIM | MILLIMETERS |      | INCHES    |       |
|-----|-------------|------|-----------|-------|
|     | MIN         | MAX  | MIN       | MAX   |
| A   | 1.90        | 2.10 | 0.075     | 0.083 |
| B   | 2.20        | 2.40 | 0.087     | 0.094 |
| C   | 0.60        | 0.90 | 0.024     | 0.035 |
| D   | 0.17        | 0.25 | 0.007     | 0.010 |
| F   | 0.20        | 0.35 | 0.008     | 0.014 |
| G   | 0.50 BSC    |      | 0.020 BSC |       |
| H   | 0.40 REF    |      | 0.016 REF |       |
| J   | 0.10        | 0.18 | 0.004     | 0.007 |
| K   | 0.00        | 0.10 | 0.000     | 0.004 |
| L   | 3.00        | 3.20 | 0.118     | 0.126 |
| M   | 0°          | 6°   | 0°        | 6°    |
| N   | 5°          | 10°  | 5°        | 10°   |
| P   | 0.23        | 0.34 | 0.010     | 0.013 |
| R   | 0.23        | 0.33 | 0.009     | 0.013 |
| S   | 0.37        | 0.47 | 0.015     | 0.019 |
| U   | 0.60        | 0.80 | 0.024     | 0.031 |
| V   | 0.12 BSC    |      | 0.005 BSC |       |

### SOLDERING FOOTPRINT\*




\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

# NL17SZ74

## PACKAGE DIMENSIONS

UDFN8, 1.45x1, 0.35P  
CASE 517BZ  
ISSUE O




### NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.20 MM FROM TERMINAL TIP.
4. PACKAGE DIMENSIONS EXCLUSIVE OF BURRS AND MOLD FLASH.

| DIM | MILLIMETERS |      |
|-----|-------------|------|
|     | MIN         | MAX  |
| A   | 0.45        | 0.55 |
| A1  | 0.00        | 0.05 |
| A3  | 0.13 REF    |      |
| b   | 0.15        | 0.25 |
| D   | 1.45 BSC    |      |
| E   | 1.00 BSC    |      |
| e   | 0.35 BSC    |      |
| L   | 0.25        | 0.35 |
| L1  | 0.30        | 0.40 |

### RECOMMENDED SOLDERING FOOTPRINT\*






DIMENSIONS: MILLIMETERS

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

# NL17SZ74

## PACKAGE DIMENSIONS


UDFN8, 1.95x1.0, 0.5P  
CASE 517CA  
ISSUE A



### NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009.
2. CONTROLLING DIMENSION: MILLIMETERS
3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.20 MM FROM THE TERMINAL TIP.
4. COPLANARITY APPLIES TO ALL THE TERMINALS.
5. PACKAGE DIMENSIONS EXCLUSIVE OF BURRS AND MOLD FLASH.

| DIM | MILLIMETERS |      |      |
|-----|-------------|------|------|
|     | MIN.        | NOM. | MAX. |
| A   | 0.45        | 0.50 | 0.55 |
| A1  | 0.00        | ---  | 0.05 |
| A3  | 0.13 REF    |      |      |
| b   | 0.15        | 0.20 | 0.25 |
| D   | 1.85        | 1.95 | 2.05 |
| E   | 0.90        | 1.00 | 1.10 |
| e   | 0.50 BSC    |      |      |
| L   | 0.25        | 0.30 | 0.35 |
| L1  | 0.30        | 0.35 | 0.40 |





\* For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

# NL17SZ74

## PACKAGE DIMENSIONS

UQFN8, 1.4x1.2, 0.4P  
CASE 523AS  
ISSUE A




### NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.25 mm FROM THE TERMINAL TIP.

| MILLIMETERS |      |      |
|-------------|------|------|
| DIM         | MIN  | MAX  |
| A           | 0.45 | 0.55 |
| A1          | 0.00 | 0.05 |
| A3          | 0.13 | REF  |
| b           | 0.15 | 0.25 |
| D           | 1.40 | BSC  |
| E           | 1.20 | BSC  |
| e           | 0.40 | BSC  |
| L           | 0.20 | 0.40 |
| L1          | ---  | 0.15 |
| L2          | 0.30 | 0.50 |

### SOLDERING FOOTPRINT\*




DIMENSIONS: MILLIMETERS

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.


# NL17SZ74

## PACKAGE DIMENSIONS


UQFN8, 1.6x1.6, 0.5P  
CASE 523AN  
ISSUE O




TOP VIEW




SIDE VIEW



BOTTOM VIEW



DETAIL B  
OPTIONAL  
CONSTRUCTION




DETAIL A  
OPTIONAL  
CONSTRUCTION

### NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.30 mm FROM THE TERMINAL TIP.

| MILLIMETERS |      |      |
|-------------|------|------|
| DIM         | MIN  | MAX  |
| A           | 0.45 | 0.60 |
| A1          | 0.00 | 0.05 |
| A3          | 0.13 | REF  |
| b           | 0.15 | 0.25 |
| D           | 1.60 | BSC  |
| E           | 1.60 | BSC  |
| e           | 0.50 | BSC  |
| L           | 0.35 | 0.45 |
| L1          | ---  | 0.15 |
| L3          | 0.25 | 0.35 |

### SOLDERING FOOTPRINT\*



DIMENSIONS: MILLIMETERS

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor  
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA  
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
Email: [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

N. American Technical Support: 800-282-9855 Toll Free  
USA/Canada  
Europe, Middle East and Africa Technical Support:  
Phone: 421 33 790 2910

ON Semiconductor Website: [www.onsemi.com](http://www.onsemi.com)

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative