

Part Number : [2300304000](#)

Product Description : MiniCirc Socket Connector,
Vertical, Gold (Au) Plating, 4 Circuits, Blue

Series Number : 230030

Status : Active

Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[2300304000 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2300300000-PS-000.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

[Substances of Interest](#)

- PFAS

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	230030
Description	MiniCirc Socket Connector, Vertical, Gold (Au) Plating, 4 Circuits, Blue
Application	Wire-to-Board
Component Type	PCB Receptacle
Product Name	MiniCirc
UPC	198930705581

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V DC

Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Blue
Durability (mating cycles max)	200
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Locking Type	Snap Lock
Material - Metal	High Performance Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Polyamide (PA)

Number of Rows	0
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	No
Pitch - Mating Interface	N/A
Pitch - Termination Interface	N/A
Plating min - Mating	0.250µm
Plating min - Termination	0.025µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-25° to +85°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
MiniCirc Female-to-Female Wiring Harnesses	<u>230031</u>
MiniCirc Female-to-Male Wiring Harnesses	<u>230032</u>

This document was generated on Jul 06, 2026