

4036B

1x15 RF Distribution Amplifier



4036B 1x15 RF Distribution Amplifier

Features

- Low phase noise
- High channel isolation
- 15 outputs
- Yields 225 outputs at second level
- LED status indicators for all inputs and outputs
- Status information via Ethernet
- Setable gain
- CE compliant

The Microsemi 4036B is a one-input, fifteen-output RF distribution amplifier in a 1U chassis. It provides fifteen isolated copies of a single input. The unit operates over a frequency range of 1 MHz to 20 MHz. Fault sensing of signal level is provided on the input and every output. Faults are indicated on the front panel LEDs, as well as via an Ethernet interface.

Microsemi makes no warranty, representation, or guarantee regarding the information contained herein or the suitability of its products and services for any particular purpose, nor does Microsemi assume any liability whatsoever arising out of the application or use of any product or circuit. The products sold hereunder and any other products sold by Microsemi have been subject to limited testing and should not be used in conjunction with mission-critical equipment or applications. Any performance specifications are believed to be reliable but are not verified, and Buyer must conduct and complete all performance and other testing of the products, alone and together with, or installed in, any end-products. Buyer shall not rely on any data and performance specifications or parameters provided by Microsemi. It is the Buyer's responsibility to independently determine suitability of any products and to test and verify the same. The information provided by Microsemi hereunder is provided "as is, where is" and with all faults, and the entire risk associated with such information is entirely with the Buyer. Microsemi does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other IP rights, whether with regard to such information itself or anything described by such information. Information provided in this document is proprietary to Microsemi, and Microsemi reserves the right to make any changes to the information in this document or to any products and services at any time without notice.

4036B

Specifications

Electrical Specifications

- RF Output (15)
 - Frequency: 1 MHz – 20 MHz
 - Input level: 0 to 1 Vrms (13 dBm)
 - Gain: 0 dB, jumper selectable –1 dB, 1 dB or 2 dB
 - Input/output impedance: 50 Ω
 - Isolation: >100 dB
 - Spurious distortion: <–80 dBc
 - Harmonic distortion: <–40 dBc
 - Connectors: BNC female
- Additive SSB Phase Noise
 - 1Hz: –135 dBc
 - 10Hz: –145 dBc
 - 100Hz: –155 dBc
 - 1kHz: –163 dBc
 - 10kHz+: –163 dBc
- Status
 - Senses signal presence on all inputs and outputs
 - Green/Red LEDs on front panel
 - LED Indicators for 1 MHz, 5 MHz, and 10 MHz
 - Network interface
 - Ethernet 10/100 Base T
 - RJ 45 connector
 - Protocols: TCP/IP, UDP/IP, ARP, Telnet, DHCP, BOOTP, HTTP and AutolP

Environmental and Physical Specifications

- Temperature: 0 °C to 50 °C
- Humidity: 0 to 95% non-condensing
- Power requirements (AC Input): 90–264 VAC, 10 W, 47–63 Hz
- Dimensions: 1.75" (4.44 cm) H x 19" (48.26 cm) W x 12" (30.48 cm) D
- Weight: 9 lb (4.10 kg)

Standards

- Safety: IEC 61010-1:2010 / EN 61010-1:2010
- EMC: EN61326-1 (2006) EMC Requirements for Measurement, Control and Laboratory Equipment, Class A
- EN61000-3-2 (2006) +A1+A2 Harmonic Current Emissions
- EN61000-3-3 (2008) Voltage Fluctuation and Flicker Emissions

Ordering Information

(Contact Microsemi for pricing and availability)

4036B Standard Configuration TSC 4036B



Rear view



Microsemi Corporate Headquarters
 One Enterprise, Aliso Viejo, CA 92656 USA
 Within the USA: +1 (800) 713-4113
 Outside the USA: +1 (949) 380-6100
 Sales: +1 (949) 380-6136
 Fax: +1 (949) 215-4996
 email: sales.support@microsemi.com
 www.microsemi.com

Microsemi Corporation (Nasdaq: MSCC) offers a comprehensive portfolio of semiconductor and system solutions for aerospace & defense, communications, data center and industrial markets. Products include high-performance and radiation-hardened analog mixed-signal integrated circuits, FPGAs, SoCs and ASICs; power management products; timing and synchronization devices and precise time solutions, setting the world's standard for time; voice processing devices; RF solutions; discrete components; enterprise storage and communication solutions, security technologies and scalable anti-tamper products; Ethernet solutions; Power-over-Ethernet ICs and midspans; as well as custom design capabilities and services. Microsemi is headquartered in Aliso Viejo, Calif., and has approximately 4,800 employees globally. Learn more at www.microsemi.com.

©2016 Microsemi Corporation. All rights reserved. Microsemi and the Microsemi logo are registered trademarks of Microsemi Corporation. All other trademarks and service marks are the property of their respective owners.