



Data Sheet | Item Number: 210-196
Aluminum carrier rail; 35 x 8.2 mm; 1.6 mm thick; 2 m long; unslotted; similar to EN 60715; silver-colored
<https://www.wago.com/210-196>



Color: ■ silver-colored



Dimensions in mm

Physical data		
Width		2000 mm / 78.74 inches
Height		8.2 mm / 0.323 inches
Depth		35 mm / 1.378 inches

Material data		
Color		silver-colored
Fire load		0 MJ
Weight		400 g

Commercial data		
Product Group		2 (Terminal Block Accessories)
PU (SPU)		20 (1) pcs
Packaging type		Box
Country of origin		DE
GTIN		4017332272315
Customs tariff number		76042990900

Product Classification		
UNSPSC		39121702
eCl@ss 10.0		27-40-06-02
eCl@ss 9.0		27-40-06-02
ETIM 9.0		EC001285
ETIM 8.0		EC001285
ECCN		NO US CLASSIFICATION



Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 210-196	

Documentation

Bid Text			
210-196	19.02.2019	xml 2.65 KB	
210-196	31.08.2017	doc 24.00 KB	

CAD/CAE-Data

CAD data		CAE data	
2D/3D Models 210-196		EPLAN Data Portal 210-196	
		WSCAD Universe 210-196	
		ZUKEN Portal 210-196	

1 Compatible Products

1.1 Optional Accessories

1.1.1 Installation

1.1.1.1 Mounting accessories

Item No.: 209-137 Mounting adapter; can be used as end stop; 6.5 mm wide; gray	Item No.: 249-117 Screwless end stop; 10 mm wide; for DIN-rail 35 x 15 and 35 x 7.5; gray	Item No.: 249-197 Screwless end stop; 14 mm wide; for DIN-rail 35 x 15 and 35 x 7.5; gray	Item No.: 249-116 Screwless end stop; 6 mm wide; for DIN-rail 35 x 15 and 35 x 7.5; gray



1.1.2 Marking

1.1.2.1 Label



Item No.: 210-808
Labels; for Smart Printer; 9.5 x 25 mm;
white



Item No.: 210-708
Labels; for TP printers; 9.5 x 25 mm; white

Installation Notes

DIN-Rail	Item No.	Current [A]	Acc. to mm ² /AWG/GU
DIN 35 x 7.5 (steel)			
slotted	210-112	76	16/6
unslotted	210-113	76	16/6
DIN 35 x 15 (steel)			
1.5 mm thick	210-114	125	35/2
2.3 mm thick	210-118	125	35/2
DIN 35 x 7.5 (Al)			
unslotted	210-196	76	16/6
DIN 35 x 15 (Cu)			
2.3 mm thick	210-198	309	150/6/0
Current applies to rails of 1 m/3'3" length			

When using standard DIN-rails as ground conductor busbars, please refer to the maximum current capacities listed above. Steel DIN-rails are not suited for PEN (ground and N-conductor) applications per EN 60947-7-2 (VDE 0611, Part 3).