




	1	2	3	4	5	6	7																																																																																					
A	 0,6 19,0 4,0 7,62 $\langle N-1 \rangle \times 7,62$ 0,90 2,95X3,8 5,0 10,5																																																																																											
B	 0,6 $N \times 7,62$ 0,6																																																																																											
C	P.C.B LAYOUT  $\langle 10,5 \rangle$ $\langle 5,0 \rangle$ $\langle 4,4 \rangle$ $\langle N-1 \rangle \times 7,62$ $\langle 4,4 \rangle$ $\varnothing 1,60$																																																																																											
D	Material Terminal body (metal housing): Brass(CuZn) Terminal screw: Steel Zinc plating "-" slot type Contacts: Brass Surface of solder tail: Tin plated Insulator (housing): Thermoplastic (UL94V-0), Green Electrical Voltage rating: 300VAC Current rating: 20A Solid wire(AWG): 12-30 Stranded wire(AWG): 12-30 Torque(Lb-in): 3.5 Screw: M3 Wire strip length: 6-7mm Withstanding Voltage: 1.6KV Operating temperature: -40°C to +115°C Soldering temperature: 250°C±10°C/5 Sec Safety Approval:  US																																																																																											
E																																																																																												
F	N=Number of contacts																																																																																											
G	RoHS compliant  File No.: E349947 <table><tr><th>Scale</th><th>1:1</th><th></th><th></th><th></th><th></th><th></th></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.</td><td>±0.50</td><td></td><td></td><td></td><td>Drawn</td><td>29.07.2009</td></tr><tr><td>X.X</td><td>±0.30</td><td></td><td></td><td></td><td>Approved</td><td>19.04.2016</td></tr><tr><td>X.XX</td><td>±0.10</td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X. °</td><td>±1°</td><td></td><td></td><td></td><td>19.04.2016</td><td>Winnie</td></tr><tr><td>X.X°</td><td>±X°</td><td></td><td></td><td></td><td>29.07.2009</td><td>Dean</td></tr><tr><td>Angle</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td></tr></table> <table><tr><th>Id.</th><th>Modification</th><th>Date</th><th>Name</th><th></th><th></th><th></th></tr><tr><td>②</td><td>Add the UL File No.</td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>①</td><td>Drawn</td><td></td><td></td><td></td><td></td><td></td></tr></table> Customer-No. ASSMANN WSW-No. A-TB762-VJxxH Drawing-No. ASS 3596 CO rev02 Replace Sheet							Scale	1:1						TOLERANCE							X.	±0.50				Drawn	29.07.2009	X.X	±0.30				Approved	19.04.2016	X.XX	±0.10						DIM	TOL						X. °	±1°				19.04.2016	Winnie	X.X°	±X°				29.07.2009	Dean	Angle	TOL						Id.	Modification	Date	Name				②	Add the UL File No.						①	Drawn						
Scale	1:1																																																																																											
TOLERANCE																																																																																												
X.	±0.50				Drawn	29.07.2009																																																																																						
X.X	±0.30				Approved	19.04.2016																																																																																						
X.XX	±0.10																																																																																											
DIM	TOL																																																																																											
X. °	±1°				19.04.2016	Winnie																																																																																						
X.X°	±X°				29.07.2009	Dean																																																																																						
Angle	TOL																																																																																											
Id.	Modification	Date	Name																																																																																									
②	Add the UL File No.																																																																																											
①	Drawn																																																																																											
H	<table><tr><td>1</td><td>2</td><td>3</td><td>4</td><td>5</td><td>6</td><td>7</td></tr></table>							1	2	3	4	5	6	7																																																																														
1	2	3	4	5	6	7																																																																																						