




REV. 0


DCO 16707

COIL: @ 25°C  
 RESISTANCE \_\_\_\_\_ 675 OHMS ± 10%  
 NOMINAL VOLTAGE \_\_\_\_\_ 26.5 VDC  
 MUST OPERATE \_\_\_\_\_ 13.5 VDC  
 \_\_\_\_\_  
 MUST RELEASE \_\_\_\_\_ 2.3 VDC

ENVIRONMENT:

VIBRATION \_\_\_\_\_ 10 \_\_\_\_\_ CPS TO \_\_\_\_\_ 2000 \_\_\_\_\_ CPS @ \_\_\_\_\_ 20 \_\_\_\_\_ g's  
 SHOCK \_\_\_\_\_ 100 \_\_\_\_\_ g's \_\_\_\_\_ 6 \_\_\_\_\_ MS. DURATION  
 TEMPERATURE \_\_\_\_\_ -65 \_\_\_\_\_ °C TO \_\_\_\_\_ +125 \_\_\_\_\_ °C  
 NOTES: OPERATE & RELEASE 6 MS MAX.  
 CONTACT BOUNCE 1 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: 2A 28 VDC  
 RESISTIVE 100,000 OPERATIONS

DR. PBB. 1/5/01

CK.TLG 1-5-01

**CI Technologies**  
 advanced control electronic solutions

CUST. \_\_\_\_\_ OPL  
 CUST. NO. M5757/10-037 REV. \_\_\_\_\_

\*FW\* RELAY

FW1167G06