



**Part Number :** [39012025](#)

**Product Description :** Mini-Fit Jr. Receptacle Housing, Dual Row, 2 Circuits, UL 94V-0, Natural

**Series Number :** 5557

**Status :** Active

**Product Category :** Connector Housings

**Engineering Number :** 5557-02R-210



---

## Documents & Resources

### Drawings

[039012025 sd.pdf](#)

[PK-5557-002-000.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[55560001-AS-000.pdf](#)

[55560002-AS-000.pdf](#)

[AS-5557-001-001.pdf](#)

[PS-45750-001-001.pdf](#)

[55560002-PS-CH-000.pdf](#)

[55560002-PS-ES-000.pdf](#)

[55560002-PS-SK-000.pdf](#)

[PS-5556-001-001.pdf](#)

[PS-5556-002-001.pdf](#)

[55560010-TS-000.pdf](#)


[TS-5556-002-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
------------	--------------

China RoHS	per SJ/T 11365-2006 
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

#### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Connector Housings
Series	5557
Description	Mini-Fit Jr. Receptacle Housing, Dual Row, 2 Circuits, UL 94V-0, Natural
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. See Molex product specification PS-45750-001 for additional current derating information.

Product Name	Mini-Fit Jr.
UPC	800753584273

## Agency

CSA	LR19980
UL	E29179

## Physical

Breakaway	No
Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	0.663/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Mini-Fit TPA2 Plug Housing, 4.20mm Pitch, Dual Row, UL 94V-0, Low-Halogen, 2 Circuits	<u>1727620002</u>

Mini-Fit TPA2 Plug Housing, 4.20mm Pitch, Dual Row, UL 94V-0, Low-Halogen, 2 Circuits, Panel Mount	<a href="#"><u>1727670002</u></a>
Mini-Fit TPA2 Plug Housing, 4.20mm Pitch, Dual Row, UL 94V-2, Glow-Wire Capable, 2 Circuits, Panel Mount	<a href="#"><u>1727670102</u></a>
Mini-Fit BMI Right-Angle Dual Row Headers	<a href="#"><u>42404</u></a>
Mini-Fit BMI Vertical Dual Row Headers	<a href="#"><u>42440</u></a>
Mini-Fit BMI Right-Angle Dual Row Headers	<a href="#"><u>43810</u></a>
Mini-Fit BMI Vertical Dual Row Headers	<a href="#"><u>44068</u></a>
Mini-Fit Jr. Dual Row Test Plugs	<a href="#"><u>44281</u></a>
Mini-Fit Jr. Plug Housings	<a href="#"><u>5559</u></a>
Mini-Fit Jr. Vertical Headers	<a href="#"><u>5566</u></a>
Mini-Fit Jr. Right-Angle Headers	<a href="#"><u>5569</u></a>
Mini-Fit Jr. Dual Row Headers	<a href="#"><u>87427</u></a>

### Use with Part(s)

Description	Part Number
Pre-Crimped Lead Mini-Fit Female-to-Mini-Fit Female, Tin (Sn) Plating, 150.00mm Length, 18 AWG, Red	<a href="#"><u>797580001</u></a>
Pre-Crimped Lead Mini-Fit Female-to-Mini-Fit Female, Tin (Sn) Plating, 300.00mm Length, 18 AWG, Red	<a href="#"><u>797580009</u></a>
Mini-Fit Female Crimp Terminals	<a href="#"><u>5556</u></a>
Mini-Fit Plus Female Crimp Terminals	<a href="#"><u>45750</u></a>
Mini-Fit Jr. Hermaphroditic Backshells	<a href="#"><u>204723</u></a>
Mini-Fit HCS Female Crimp Terminals	<a href="#"><u>44476</u></a>

---

This document was generated on Sep 05, 2025