



Part Number : 365350001
Product Description : MLX Crimp Terminal
42024, 16-14 AWG, Reel, Tin (Sn)
Series Number : 36535
Status : Active
Product Category : Crimp Terminals




Documents & Resources

Drawings
[365350001_sd.pdf](#)

Specifications
[PS-42022-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	36535
Description	MLX Crimp Terminal 42024, 16-14 AWG, Reel, Tin (Sn)
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	MLX
UPC	800754799348

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.453/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	5.10mm max.
Wire Size (AWG)	14, 16
Wire Size mm ²	1.30-2.00

Use with Part(s)

Description	Part Number
2.13mm Diameter MLX Power Crimp Housing Plugs	<u>42021</u>
MLX Crimp Terminals	<u>36663</u>
MLX Female Terminals	<u>36664</u>

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for Crimp Terminals	<u>638199500</u>
T2 Terminator Die	<u>638533000</u>
FineAdjust Applicator	<u>638633000</u>

This document was generated on Mar 14, 2025