





PRODUCT NUMBER	PITCH
T7xx03x000J0G	6.35 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW



PART NO.: T7 xx 0 3 x 0 00J0 G

N = Number of poles
Dim A=Nx6.35
Dim B=(N-1)x6.35

Poles	Tolerance
2-6p	±0.15
7-11p	±0.25
12-16p	±0.35

End Stackable	Body Color	RoHS compliant (lead<4%)
No. of poles	0 Black (RAL9005)	In copper Alloy
02 2 poles	2 Red (RAL3001/D)	
03 3 poles	3 Orange(RAL2011/P)	
...	4 Yellow(RAL1018/A)	
16 16 poles	5 Green(RAL6018/T)	
	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	
	9 White(RAL1102)	
	C Green(RAL6018/U)	

Material:

- Item ① Terminal housing : Thermoplastic (UL 94V-0)
- Item ② Clamp : Brass , Ni plated
- Item ③ Solder pin : Copper , Tin plated
- Item ④ Terminal screw: Steel Zinc plating"-slot type

Electrical cULus TUV

- Voltage rating: 300VAC 450VAC
- Current rating: 30A 41A
- Wire range:
 - Solid wire(AWG): 10-24
 - Stranded wire(AWG): 10-24
- Torque: 6.9 Lb-in 0.85 N.m
- Screw: M3.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV 2.5KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus TUV

mat'l. code				surface	tolerance	projection	product family
Itr	ecn no	dr	date	ASME Y14.5	ASME Y14.5		TERMINAL BLOCK
B	T-19284	HF	081414	tolerances unless otherwise specified			title
				angles	X.±0.5	MM	TERMINAL BLOCK
				edges	X.X±0.3		RISING CLAMP,180D WIRE INLET,END STACKABLE
				XX.±1°	XXX±0.1	scale	
				dr	EVIN ZHONG 041414		dwg no
				engr	EVIN ZHONG 041414		sheet 1 of 1
				chr	HANKE FENG 041414		size
				appd	SHI JUN 041414		A4
				sheet	revision	B	
				index	sheet	1	

