

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1554216010

Status:

Active

Overview:

Flamar Standard Cables for Industrial Automation

Description:

Flamar Ethernet 5e Network Cable, WSOR Jacket, Braided Shielding Overall, 8 Circuits, 4x(2x0.25mm²) / 4x(2x24 AWG), 7.80mm (.307") Diameter, 300.0m (984.25') Length, Teal

Documents:

Product Specification 1554216001-P1E (PDF)

Product Literature (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable
Series	155421
Comments	3 reels of 100.0m each
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	Flamar Standard Cables for Industrial Automation
Product Literature Order No	987651-3992
Product Name	Flamar
Protocol	EtherNet 5e
UPC	889056465007
Physical	
Bending Radius - Minimum	> 15xOD
Cable Length	300.0m
Circuits (Loaded)	8
Color - Cable Jacket	Teal
Insulation	PE
Material - Outer Jacket	WSOR
Net Weight	0.010/g
Outer Jacket Diameter	7.80mm
Packaging Type	Reel
Temperature Range - Operating	-10°C to +60°C
Wire Size AWG	24
Wire Size mm²	0.25
Wire/Cable Type	UL AWM 21215 / CSA
Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	600V
Material Info	
Engineering Number	3X100M
Reference - Drawing Numbers	
Product Specification	1554216001-P1E



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Not Reviewed

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

155421 Series

Use With

Micro-Change® (M12) 130047 , 120100 , 130034 , 120071

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION