

**Part Number :** [1718573006](#)

**Product Description :** KK 254 RPC Right-Angle Header, 2.54mm Pitch, Friction Lock, Reflowed Matte Tin (Sn) Plating, 6.73mm Mating Pin Length, 2.54mm Tail Length, Tape and Reel, 6 Circuits

**Series Number :** 171857

**Status :** Active

**Product Category :** PCB Headers and Receptacles



---

## Documents and Resources

### Drawings

[1718573006 sd.pdf](#)

[PK-171857-0001-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[SYM-171857-0006-001.zip](#)

### Specifications


[PS-171856-0001-001.pdf](#)

[PS-171856-0002-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	PCB Headers and Receptacles
Series	171857
Description	KK 254 RPC Right-Angle Header, 2.54mm Pitch, Friction Lock, Reflowed Matte Tin (Sn) Plating, 6.73mm Mating Pin Length, 2.54mm Tail Length, Tape and Reel, 6 Circuits
Application	Power, Signal, Wire-to-Board, Board-to-Board
Component Type	PCB Header
Product Name	KK 254
UPC	887191716336

### Agency

CSA	LR19980
UL	E29179

## Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V AC

## Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-1
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Nylon
Net Weight	0.786/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.60mm
PC Tail Length	2.54mm
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	1.524µm
Plating min - Termination	1.524µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Partially Shrouded

Stackable	Yes
Temperature Range - Operating	-40° to +80°C
Termination Interface Style	Through Hole

### Solder Process Data

Max-Duration	30
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	3
Max-Temp	260

---

### Mates With / Use With

#### Mates with Part(s)

Description	Part Number
KK 254 Single Row Crimp Housings	<u>2695</u>
KK 254 PC Board Connector	<u>4455</u>

---

This document was generated on May 17, 2026