


REV.	DESCRIPTION		DATE	APPROVED
01	RELEASED PER E980365	DPK	9/14/98	RCM
02	REVSD- E980451	RCM	12/11/98	DPK
03	REVSD PER E990386	AK	9/14/99	RCM
04	REVSD PER E990450	RCM	3/6/00	DPK
5	REVISED PER E050121	LEK	05/16/05	CF
6	REVISED PER ECO Request E080724	REJH	04/09/08	EF

VICOR HUB PART NO.	MATING CONNECTOR		
	ORDER FROM: AMP		ORDER FROM: VICOR
	HOUSING (QTY 1)	PINS (QTY 2)	HOUSING/PINS KIT (QTY 1)
HUB470-P	770017-1	770248-1	21395



NON
CONDUCTIVE
COVER

NON
CONDUCTIVE
BASE

AT +105°C, 120HZ UNLESS OTHERWISE NOTED						
ITEM		CHARACTERISTICS				
OPERATING TEMPERATURE		-25 to +105°C				
CAPACITANCE TOLERANCE @+20°C		±20%				
		AMBIENT TEMPERATURE (°C)				
		+45	+60	+70	+85	+105
RIPPLE CURRENT MULTIPLIER		2.64	2.23	2.12	1.73	1.00
DISSIPATION FACTOR @ +20°C		0.1				
RATED VOLTAGE (WVDC)		450				
CAPACITANCE VALUE (C1, C2 EA. uF)		470				
MAXIMUM ESR (OHMS) @ +20°C		0.529				
MAXIMUM RIPPLE CURRENT (A rms)		1.72				

NOTES;

1. RoHS COMPLIANT, LEAD FREE PER
CST-0001 LATEST REVISION.

DRAWN BY <i>D.CYNAR</i>		DATE <i>4/2/98</i>			
UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES. TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ±1/64 .XX±.01 ±° .XXX±.005					
THIRD ANGLE PROJECTION		SIZE C	FSCM NO. 67131	DWG NO 16769	REV. 6
 DO NOT SCALE DRAWING		SCALE FULL		SHEET 1 OF 1	