


39516300000 - 395 Series



Series: 395

 [Fuse 395 Datasheet](#)

- Features:**
- Reduced PCB space requirements
 - Direct solderable or plug-in versions
 - Internationally approved
 - Low internal resistance
 - Shocksafe casing
 - Vibration resistant
 - Halogen free
 - CCCe for China import

Click on part number below for individual TC curve files.

Questions? [Contact Littelfuse Support](#)

 [Check Stock](#)

 [Order Samples](#)

[Read Now](#)

[SIGN UP NOW](#)

Feedback

Electrical Characteristics		Technical Resources	Environmental Info
Property (Mouseover for details)		Value	
Ampere Rating (A)		6.3	
Nominal Melting I ² T (A ² sec)		9.7	
Interrupting Rating		100A@125VAC	
Min Operating Temp °C		-40	
Max Operating Temp (°C)		85	
Moisture Sensitivity Level		MIL-STD-202 Method 106	
Nominal Power Dissipation (W)		850	
Nominal Voltage Drop (mV)		115	
Nominal Cold Resistance (Ohms)		0.0116	
Opening		Fast-Acting (F)	
Package Size		TE5 (8.5x8mm)	
VAC (V)		125	

Connect with Littelfuse

Sign up to receive special offers and news

Enter your email

Submit

For more details about how we use your information, check our [Privacy Statement](#).





About Littelfuse

About Littelfuse

Conflict Free Statement

History

Investor Relations

Legal

Press Room

Privacy Statement

Supply Chain Transparency

Website Feedback

Explore Littelfuse

Capabilities Brochures

Careers

Check Distributor Stock

Competitor Cross Reference

Industries

Order Samples

Products

Services

Technical Resources

Application Designs

Education

FAQs

iDesign™

Littelfuse University

Product Catalogs

Quality Documents

Technical Documents