





SPECIFICATION	
Mating Cycles	500
Filter type	C
Capacitance	47pF±20%
Working Voltage	100v
Current Rating	7,5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION dB
5	-
10	-
50	-
100	-
500	30dB
1000	35dB



							Dat.	Name		D-Sub, Female, Straight 9 Poles, solder buckets, shell with clinch nuts	Mo?Ms lab/ Scale 1.5:1	
						Detail.	8 - JUL - 02	CV				
						Insp.						All Dim. in mm
			33440	16/03/06	JMDR	Stand.						Orig. Size DIN A 4
09641117218	M3		32803	29/09/05	JMDR	HARTING EURL F-95972 Paris					TB 0964111721x	Blatt/ Page 1 / 1
09641117217	UNC 4-40		31058	8 - JUL - 02	CV							
Part number	Nut thread		Mod.	Dat.	Name							