Data sheet

CABTITE EP 24/13 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Cabtite - Cable Entry Plates
Insert cables and wires without plugs into control cabinets, enclosures or machines in the smallest of spaces, easily and in a space-saving manner.
With the Cabtite cable entry plates, you can do this even in harsh environments, whether protective hoses, pneumatic/hydraulic hoses or fiber optic cables - you can install your cables quickly, easily and in a space-saving manner. The installation is done through only one rectangular wall cut-out and is therefore up to 40% faster in the installation time (compared to standard cable glands).
The IP66 screw version of cable entry plates are tested according to DIN EN 60529 and made of UL94 V-0 certified TPE material with hard plastic core, suitable for the temperature range from -40°C to +90°C.
Cabtite cable entry plates are an economical alternative to conventional cable glands.

General ordering data

Version	Cable entry plate, Cabtite (cable entry system), TPE, grey, Height: 58 mm, Width: 149.6 mm, Depth: 29.2 mm, -40 °C...90 °C, IP66
Order No.	2779310000
Type	CABTITE EP 24/13 GY
GTIN (EAN)	4064675048787
Qty.	10 items

Downloaded from Arrow.com.

Data sheet

CABTITE EP 24/13 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E223801

Dimensions and weights

Depth	29.2 mm	Depth (inches)	1.1496 inch
Height	58 mm	Height (inches)	2.2835 inch
Width	149.6 mm	Width (inches)	5.8898 inch
Net weight	69.1 g		

Temperatures

Operating temperature	-40 °C...90 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Tightening torque	3.5 Nm	Silicone	No
UL 94 flammability rating	V-0	Protection degree	IP66
Basic material	TPE	Protection class (UL)	Type 1, Type 12, Type 4X

Number of connectable cables

Type of mounting	4 screws	
Number of connectable cables	13	
Cable entries	Number	10
	Cable diameter, min.	3.2 mm
	Cable diameter, max.	6.3 mm
	Cable type	Round cable
	Number	3
	Cable diameter, min.	16 mm
	Cable diameter, max.	20.5 mm
	Cable type	Round cable

Classifications

ETIM 8.0	EC002624	ETIM 9.0	EC002624
ETIM 10.0	EC002624	ECLASS 14.0	27-18-28-15
ECLASS 15.0	27-18-28-15		


Downloaded from Arrow.com.

CABTITE EP 24/13 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Downloaded from Arrow.com.