

# MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY  
PROSPER, ILLINOIS

FED. MFR. CODE 91929

## SWITCH - BASIC

CATALOG LISTING

IHTI

(M)IHTI  
ISSUE 9

CATALOG LISTING

IHTI

PAGE 1 OF 1

M

DRAWING  
NUMBER

ISSUE  
19

RELEASE NO.

CHECK

CHECK

CHECK

CHECK

CHECK


CHECK

CHECK

CHECK

CHECK

CHECK



### NOTE-

- 1-SWITCH WILL WITHSTAND TEMPERATURE OF 1000°F MAX
- 2 RECOMMENDED APPLIED TORQUE FOR A 6-32 UNC STAINLESS STEEL TERMINAL IS 10 IN LB MAX. EXCEEDING THIS TORQUE COULD DAMAGE THE SWITCH

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

### CHARACTERISTICS

OPERATING FORCE — — — — — 10-20 OZ

RELEASE FORCE — — — — — 6 OZ MIN

PRETRAVEL — — — — — .065 MAX

DIFFERENTIAL TRAVEL — — — .010 MAX

OVERTRAVEL — — — — — .188 MIN

### ELECTRICAL DATA

CONTACT ARRANGEMENT  
S P D T

L305 3A 1/10HP 125 VAC  
2A 1/6HP 250 VAC



### SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED  
DIMENSIONS ARE IN INCHES  
**TOLERANCES ARE:**

|             |        |       |
|-------------|--------|-------|
| ONE PLACE   | (.0)   | ±.030 |
| TWO PLACE   | (.00)  | ±.015 |
| THREE PLACE | (.000) | ±.005 |
| ANGLES      |        | ±     |

WEIGHT 2.4 OZ MAX

FORMTEK

DRAWN

SEP 61

SEP 61

SEP 61