Part Number : 1200705209
Product Description : M12 Signal, A-Coded, Receptacle, 8 Poles, Male, Front Panel Mount, PG9 Mounting Threads, 0.25mm² (24 AWG), PVC Leads, 0.30m (0.984') Length
Series Number : 120070
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : 8R8J26E02C3003



Documents and Resources

Drawings

1200705209_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Triphenyl-phosphate per D(2025)4165-DC (25 June 2025) SCIP:0951f940-268b-45ab-af1d-9f2e3823f56d
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Connectors
Series	120070
Description	M12 Signal, A-Coded, Receptacle, 8 Poles, Male, Front Panel Mount, PG9 Mounting Threads, 0.25mm² (24 AWG), PVC Leads, 0.30m (0.984') Length
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	M12 Signal,Micro-Change (M12)
Type	Single Ended (pigtail)
UPC	884982224766

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	30V

Physical

Coupling Type	External Thread
Gender	Male

Downloaded from Arrow.com.

Keyway	A-Coded
Length	0.30m
Material - Component	Nickel-plated Brass
Mounting Thread Size	PG9
Net Weight	9.071/g
Orientation	Straight
Panel Mount	Front
Poles	8
Temperature Range - Operating	-25° to +90°C
Wire/Cable Type	UL 1061
Wire Size (AWG)	24

Downloaded from Arrow.com.