M422 Pb-free, Pt Temperature Sensor according to DIN EN IEC 60751

Temperature range -70 °C to +500 °C, temporary up to +550 °C

- Excellent long term stability and low drift
- High accuracy and interchangeability
- High vibration and shock resistance
- Optimized for welding, brazing and crimping
- Ideal choice for your large volume applications
- Contributes to environmental protection by reducing Pb in electronic products

M-series RTDs are characterized by long-term stability and excellent precision over a wide temperature range. The M422 combines performance and high volume availability. The perfect choice for pyrolytic ovens, home applicance, HVAC industries, medical devices, industrial process monitoring and more. In principle, the products can also be used in automotive applications, in this case YAGEO Nexensos will check upon the request of the customer, whether additional requirements can be met (e.g. IMDS, PPAP).

Nominal Resistance R_0 [Ω]	Tolerance Class	Order Number	Packaging
Pt100	F 0.1 (1/3 B) F 0.15 (A) F 0.3 (B)	5220275 / 5220285 5220271 / 5220283 5220031 / 5220281	Plastic bag / Blister reel Plastic bag / Blister reel Plastic bag / Blister reel
Pt500	F 0.1 (1/3 B) F 0.15 (A) F 0.3 (B)	5220274 5220273 / 5220282 5220032 / 5220284	Plastic bag Plastic bag / Blister reel Plastic bag / Blister reel
Pt1000	F 0.1 (1/3 B) F 0.15 (A) F 0.3 (B)	5220280 5220272 / 5220279 5220033 / 5220277	Plastic bag Plastic bag / Blister reel Plastic bag / Blister reel

The measuring point for the nominal resistance is 8 mm from the end of the sensor body.

Temperature Range of Tolerance Class

Validity of Class F 0.1 (1/3 B)	0 °C to +150 °C
Validity of Class F 0.15 (A)	-50 °C to +300 °C
Validity of Class F 0.3 (B)	-70 °C to +500 °C

The specified tolerance classes refer to continuous operation.
Class F 0.3 also applies up to +550 °C for short periods.

Temperature Coefficient

TCR = 3850 ppm/K

Response Time

Water (v = 0.4 m/s):	t0.5 = 0.07 s t0.9 = 0.2 s
Air (v = 2 m/s):	t0.5 = 3.2 s t0.9 = 11 s

Measuring Current

Pt100 Ω: 0.3 to 1 mA
Pt500 Ω: 0.1 to 0.7 mA
Pt1000 Ω: 0.1 to 0.3 mA
(self-heating has to be considered)

Dimensions and Tolerances in mm

L: 4.05 ±0.15
W1: 2.1 +0.4 -0.2
H: 0.75 +0.3 -0.1
LL: 10 ±1.0
Lø: 0.2 ±0.02
W2: 0.8 ±0.1




Image for illustration purposes only

YAGEO Nexensos GmbH, Germany
Web: www.yageogroup.com
Contact: nexensos.america@yageo.com

Downloaded from Arrow.com.

M422 Pb-free, Pt Temperature Sensor according to DIN EN IEC 60751

Temperature range -70 °C to +500 °C, temporary up to +550 °C

Long-Term Stability
The drift of the resistance value at 0 °C after a storage for 1000 hours in air at the declared upper temperature limit is not more than the tolerance value of the declared tolerance class according DIN EN IEC 60751.
Typical drift of R(0 °C) is 0.04 % after 1000 hours at +500 °C.

Self-Heating
0.3 K/mW at 0 °C

Insulation Resistance
> 100 MΩ at 20 °C
> 2 MΩ at 500 °C

Vibration Resistance
At least 40 g acceleration at 10 to 2000 Hz, depends on installation

Shock Resistance
At least 100 g acceleration with 8 ms half sine wave, depends on installation

Connection Technology
Crimping, Welding, Brazing

Tensile Strength of Leads
≥ 9N

Packaging
Blister reel, Plastic bag
Alternative packaging forms on request.

Storage Life
Min. 48 months (in original packaging).

Note
Other tolerances, values of resistance and wire lengths are available on request.

Due to random sample measurements, a bending of connection wires may occur (called V-shape). This bending is batch-dependent and has no influence on the functionality of the platinum measuring resistor.

Pb concentration is below 1000 ppm for each homogeneous material in the product.

California Proposition 65

WARNING

WARNING: This product can expose you to chemicals including lead oxide, which is known to the State of California to cause cancer and birth defects or other reproductive harm, and including cobalt oxide, nickel and cobalt, which are known to the State of California to cause cancer.
For more information go to www.p65warnings.ca.gov

The information provided in this data sheet describes certain technical characteristics of the product, but shall not be qualified or construed as quality guarantee (Beschaffenheitsgarantie) in the meaning of sections 443 and 444 German Civil Code. The information provided in this data sheet regarding measurement values (including, but not limited to, response time, long-term stability, vibration and shock resistance, insulation resistance and self-heating) are average values that have been obtained under laboratory conditions in tests of large numbers of the product. Product results or measurements achieved by customer or any other person in any production, test, or other environment may vary depending on the specific conditions of use. YAGEO Nexensos does not recommend the use of standard catalogue products or automotive grades for aerospace applications or manned space flight. The customer is solely responsible to determine whether the product is suited for the customer's intended use; in this respect YAGEO Nexensos cannot assume any liability. The sale of any products by YAGEO Nexensos is exclusively subject to the General Terms of Sale and Delivery of YAGEO Nexensos in their current version at the time of purchase, which is available under www.yageogroup.com/SalesResources/ResourceLibrary or may be furnished upon request. This data sheet is subject to changes without prior notice.

YAGEO Nexensos GmbH, Reinhard-Heraeus-Ring 23, 63801 Kleinostheim, Germany

Downloaded from Arrow.com.