





REV.	DATE	DESCRIPTION
NC	05/24/05	INITIAL RELEASE
A	10/01/06	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex						
7						DRAWN	G.R.S.	10/02/06								
6						CHECKED			PART DESCRIPTION BNC CRIMP PLUG – RG11/U 14–AWG CONTACT (FOR BELDEN 9292, 8213 CABLE – 75ohm)							
5						ISSUED										
4	FERRULE	COPPER	NICKEL	1		SHEET	1 OF 1		PART NO. 112606							
3	CONTACT PIN	BRASS	GOLD	1	CAD FILE C:/112/112606.DWG											
2	INSULATOR	TEFLON	NATURAL	1	DWG. NO.				112606.DWG		REV.	A	SIZE	A	SCALE	NA
1	BODY	BRASS	NICKEL	1												
	DESCRIPTION	MATERIAL	FINISH	QTY												