Data sheet

ZQV 16/2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Accessories, Cross-connector, 76 A
Order No.	1739690000
Type	ZQV 16/2
GTIN (EAN)	4008190957148
Qty.	25 items

Downloaded from Arrow.com.

Data sheet

ZQV 16/2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	35.1 mm	Depth (inches)	1.3819 inch
Height	20.6 mm	Height (inches)	0.811 inch
Width	5.2 mm	Width (inches)	0.2047 inch
Net weight	9.9 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-60 °C...85 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

System specifications

Version	For the terminals

Additional technical data

Type of fixing	Plugged	Explosion-tested version	Yes

Dimensions

Pitch in mm (P)	12.00 mm

General

Number of poles	2

Rating data

Rated voltage	400 V	Nominal current	76 A

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		

Downloaded from Arrow.com.