Part Number : 346916160
Product Description : Stac64 Right-Angle Header Assembly, Plastic Pin-Alignment-Plate, 16 Circuits, Polarization A, Black, Tray
Series Number : 34691
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

346916160_sd.pdf

PK-31300-892-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

347290200-AS-CH-000.pdf

PS-34729-020-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	34691
Description	Stac64 Right-Angle Header Assembly, Plastic Pin-Alignment-Plate, 16 Circuits, Polarization A, Black, Tray
Application	Automotive, Wire-to-Board
Comments	Polarization A
Component Type	PCB Header
Product Name	Stac64
UPC	887191003702

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	500V

Physical

Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16

Downloaded from Arrow.com.

Color - Resin	Black
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	7.649/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	No
PCB Thickness - Recommended	1.57mm
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	40
Lead-Free Process Capability	WAVE
Max-Cycle	3
Max-Temp	260

Mates With / Use With

Downloaded from Arrow.com.

Mates with Part(s)

Description	Part Number
Stac64 Receptacle Housings	34729

Downloaded from Arrow.com.