

★★★★★

0 Reviews

★★★★★

0 Reviews

Need Help?

[Browse All Products](#)

[USB](#)

[USB-C Cables and Adapters](#)

[USB-C Cables](#)

Loading...

6ft USB 3.0 USB-C to USB-A Cable M/M - Black

Power, charge, and transfer data to and from any standard USB-C device and a USB-A device or accessory.

★★★★★

0 Reviews

Roll over image to zoom in

Product # : 28832

Connector 1 : (1) USB-C Male

Connector 2 : (1) USB-A Male

Lengths :

6ft3ft10ft

1,084 In Stock & ready to ship!

1

Add

VISA

MasterCard

AMERICAN EXPRESS

discover

PayPal

pay

Need it shipped today?

Place your order before the timer runs out!

08: 44: 35

print

share

chat

Product Info

★ Customer Reviews

Questions & Answers

Distributors

More Choices

Description

Features

Specs

Support

Product Description

The USB-C to A 3.0 Male to Male Cable is the perfect solution for connecting any standard USB-C enabled device to a USB-A device or accessory for charging and data transfer.

Ensure that a USB-C equipped laptop, smartphone, or tablet is fully charged and ready to go from the 3A charging output, while simultaneously transferring photos, music, or data at speeds up to 5 Gbps.

The USB-C connector has a symmetrical design which is identical on both sides, so it does not matter if you plug it in upside-down or right-side-up. It will plug in the first time, every time while preventing damage to the connector port.

Product Features

- Data transfer speeds up to 5 Gbps
- 3A charging output
- Reversible, symmetrical USB-C connector
- USB IF Certified

⚠ **WARNING:** Cancer and Reproductive Harm [www.P65Warnings.ca.gov](#)

Product Specifications

Color :	Black
Length :	6.00 Foot
UPC :	757120288329
Warranty :	Lifetime

Weight :

0.171 LB

Electrical Specifications

- USB3.1~UL2725~ [30AWG(7/0.10TC)+EAM]*2P+[30AWG(7/0.10TC)+A]*1P+24AWG(41/0.08TC)*1C+EAB(16/10/0.08TC 85%TC)OD:4.8mm ~ Black
- Rated Temperature: 80°C ; Voltage: 30 V
- Max Conductor Resistance at 20°C: 30AWG , 378 OHMS/KM
- Insulation Resistance: 10M-KM MIN at 20°C DC 500V.(EIA—364—21)
- Dielectric Strength: AC 500V/1 Minute No Breakdown.(EIA—364—20)

Physical Specifications

- Operating Temperature: 0 ~ 50°C; 15-85% RH (Non-Condensing)
- Storage Temperature: -25 ~ 70°C; 15-85% RH (Non-Condensing)
- USB3.1 C Type Male:Contacts Terminal Gold Flash, Nickel Plated Shell; Black Insulation
- USB3.0 A Type Male:Contacts Terminal Gold Flash, Nickel Plated Shell; Black Insulation
- Molding Material: Black PVC Conform RoHS
- Product is CE marked and conforms to 2011/65/EU RoHS2

Product Support

Downloads

- Download the [Data Sheet](#)

Info

About Us
Order History
Where To Buy
More ▾

Service

Contact Us
OEM Solutions
Tech Support
More ▾

Resources

Connector Guides
ConnectXpress
Drivers & Manuals
More ▾

Have A Question?

Get help with [Chat](#)
Call C2G **800.506.9607**



United States | Europe +

Copyright © 2019 C2G. All Rights Reserved

