



**Part Number :** [1200060275](#)  
**Product Description :** Micro-Change (M12)  
Single-Ended Cordset, 3 Poles, Male (90°) to  
Pigtail, 0.34mm<sup>2</sup> Black PVC Cable, 5.0m  
(16.40') Length  
**Series Number :** 120006  
**Status :** Active  
**Product Category :** Circular Industrial  
Cordsets  
**Engineering Number :** 803007E03M050



Documents & Resources

Drawings  
[1200060275\\_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead... per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Circular Industrial Cordsets
Series	120006
Description	Micro-Change (M12) Single-Ended Cordset, 3 Poles, Male (90°) to Pigtail, 0.34mm <sup>2</sup> Black PVC Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Protocol	N/A
Type	Single Ended
UPC	883906067274

#### Agency

UL	E152210
----	---------

#### Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

#### Physical

Cable Diameter	4.90mm (.193")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	Single
LED Indicator	None

Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	90° to Pigtail
Poles	3
Temperature Range - Operating	-30° TO +80°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	22

---

This document was generated on Apr 26, 2025