Product data sheet

Specifications



Discontinued - Service only

APC Smart-UPS, Line Interactive, 3kVA, Tower, 230V, 8x IEC C13+1x IEC C19 outlets, SmartSlot, AVR, LCD

SMT3000I

Discontinued on: Jul 30, 2026

End-of-service on: Jul 30, 2026

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.

Main

Main input voltage	230 V AC 1 phase
Other input voltage	220 V 240 V
Input connection	IEC 320 C20 Schuko CEE 7 / EU1-16P BS1363A British
Efficiency at full load	151...302 V adjustable 160...286 V
Input frequency	50/60 Hz +/- 3 Hz auto-sensing
Output voltage	230 V AC 1 phase
Rated power in W	2700 W
Rated power in VA	3000 VA
Output connection	8 IEC 320 C13 2 IEC Jumpers 1 IEC 320 C19
Harmonic distortion	Less than 5 % at full load
Maximum configurable power in VA	3000 VA
Maximum configurable power in W	2700 W
Transfer time	2 ms typical
UPS topology	Line interactive
Waveform type	Sine wave
Output frequency	47...53 Hz for 50 Hz nominal sync to mains 57...63 Hz for 60 Hz nominal sync to mains
Replacement battery	RBC55

Graphs

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Downloaded from Arrow.com.

Complementary

Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Battery type	Lead-acid internal included
Control panel	Multifunction LCD status and control console
Emergency power off	Yes
Free slot	1
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
UPS connectivity	Serial port USB port Available expansion slot
Surge energy rating	365 J
Noise filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449
Number of rack unit	0U
Number of cables	1
Color	Black
Height	435 mm
Width	197 mm
Depth	544 mm
Product weight	52.5 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes
Mounting mode	Tower
Provided equipment	USB cable Documentation CD Smart UPS signalling RS-232 cable
Number of power modules	0
Number of power module filled slots	0
Number of power module free slots	0
Redundant	No
Range of product	Smart-UPS
Product or component type	Uninterruptible power supply (UPS)

Environment

Product certification	CE CSA EAC RCM VDE
Standard	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Ambient air temperature for operation	0…40 °C

Downloaded from Arrow.com.

Ambient air temperature for storage	-15…45 °C
Storage altitude	0…15240 m
Relative humidity	0…95 %
Storage relative humidity	0…95 %
Acoustic level	53 dBA
Heat dissipation	375 Btu/h
Operating altitude	0...10000 ft

Batteries & Runtime

Battery type	Lead-acid battery
Extendable runtime	1
Included battery module	0
Empty battery slot	0
Typical recharge time	3 h
RBC quantity	1
Battery life	3…5 year(s)
Battery charging power	271 W rated

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	69.400 cm
Package 1 Width	38.200 cm
Package 1 Length	76.200 cm
Package 1 Weight	64.000 kg
SCC14	731304268710

Contractual warranty

Warranty (in months)	24 Battery|36 UPS

Downloaded from Arrow.com.

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant By Exemption
REACh Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer

Lifetime extension

Repair	No

Use Again

Repack and remanufacture

End of life manual availability	End of Life Information
Removable battery	User replaceable
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Downloaded from Arrow.com.

Image of product / Alternate images

Alternative



Downloaded from Arrow.com.