




<https://www.wago.com/267-520>



Color: yellow

Similar to illustration



Dimensions in mm

Electrical data

Ratings per IEC/EN	
Ratings per	IEC/EN 61984
Rated voltage (III/2)	500 V
Rated impulse voltage (III/2)	4 kV
Rated current	16 A
Legend (ratings)	(III / 2) Δ Overvoltage category III / Pollution degree 2

Connection data

Number of connection types	1	Connection 1	
		Pole number	4

Material Data

Note (material data)	Information on material specifications can be found here
Color	yellow
Material group	I
Insulation material	Polyamide (PA66)
Flammability class per UL94	V0
Clamping spring material	Chrome-nickel spring steel (CrNi)
Contact material	Electrolytic copper (E _{Cu})
Contact plating	Tin
Fire load	0.273 MJ
Weight	14.9 g



Environmental requirements		
Temperature stability		105 °C

Commercial data		
Product Group		8 (Misc. Chassis Mount Blocks)
eCl@ss 10.0		27-44-03-14
eCl@ss 9.0		27-44-03-14
ETIM 8.0		EC000458
ETIM 7.0		EC000458
PU (SPU)		50 pcs
Packaging type		Box
Country of origin		PL
GTIN		4045454498986
Customs tariff number		85366990990

Approvals / Certificates		
General approvals		



Approval	Standard	Certificate Name
CCA DEKRA Certification B.V.	EN 61984	2156138.01
CCA DEKRA Certification B.V.	IEC 61984	NL-47713
UL UL International Germany GmbH	UL 1977	E45171
VDE VDE Prüf- und Zertifizierungsinstitut	EN 61984	40032309

Downloads		
Environmental Product Compliance		
Compliance Search		
Environmental Product Compliance 267-520		

Documentation			
Additional Information			
Technical Section	03.04.2019	pdf 1949.09 KB	

CAD/CAE-Data		
--------------	--	--



CAD data
2D/3D Models 267-520


CAE data
ZUKEN Portal 267-520
