




REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	MAR17/16	L.CHAN
B	CHANGE SHIELD TAIL PLATING	MAR21/17	L.CHAN
C	ADD DIM OF WIDTH BOARDLOCK	MAR29/17	L.CHAN




FRONT VIEW



SIDE VIEW



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)



RECOMMENDED PANEL CUTOUT



NOTES:

1. MATERIALS:

PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING UL 94V-0, COLOUR: BLACK

CONTACTS:

PHOSPHOR BRONZE
PLATING: 50 μ" [1.27 MICRONS]
MIN. GOLD ON MATING SURFACES.
50 μ" [1.27 MICRONS]
MIN. NICKEL UNDERPLATE
100 μ" [2.54 MICRONS]
MIN. MATTE TIN ON CONTACT TAILS.

SHIELD: STAINLESS STEEL WITH MATTE TIN PLATING ON SOLDER TAIL

2. RECOMMENDED SOLDERING TEMPERATURE:

WAVE SOLDERING AT 260°C MAXIMUM FOR 5 SEC MAXIMUM.

3. PART NUMBER: RJHSE-5M80

UNLESS SPECIFIED OTHERWISE		DRAWN	AMY.Z	DATE	MAR17/16	Amphenol Canada Corp.	
PRIMARY UNITS	INCH	CHECKED	L.CHAN		MAR17/16	www.amphenolcanada.com	
SECONDARY	MILLIMETER	M.E. APP'D				TITLE	
REFERENCE IN PARENTHESES		Q.A. APP'D				HIGH SPEED RJ45 SINGLE-PORT WITH SHIELD WITHOUT TABS AND SHIELD COVER THE LED AREA,WITHOUT LED'S - RoHS COMPLIANT	
GENERAL TOLERANCES		DWG APPR.				DWG. NO.	
1 DECIMAL PLACE	±0.025	ENG. REL. NO.				P-RJHSE-5M80	
2 DECIMAL PLACES	±0.020	REF.				REV	
3 DECIMAL PLACES	±0.015	THIRD ANGLE PROJECTION				C	
ANGULAR DEGREES	±1.0°	DO NOT SCALE DRAWING				CODE ID NO. 03554 DWG SIZE: C SCALE: N/A SHEET 1 OF 1	