


REV	DOCUMENT	CHANGED BY	CHECK
11	0034444	JA 16OCT07	PSR



RELEASE NO.:	-
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH		DRAWN	JA	16OCT07	Honeywell			
OPERATING FORCE-----3-5 OZ.		CONTACT ARRANGEMENT S P D T			TOLERANCES UNLESS NOTED:		CHECK	PSR	16OCT07				
RELEASE FORCE-----1 OZ. MIN.		30 VOLTS DC RATING			NO PLACE X ± 0.040		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH-BASIC			
		SEA LEVEL 50,000 FT			ONE PLACE .X ± 0.030								
DIFFERENTIAL TRAVEL-----.002 MAX.		INDUCTIVE 3 AMP 2.5 AMP			TWO PLACE .XX ± 0.015								
OVERTRAVEL-----.005 MIN.		RESISTIVE 5 AMP 5 AMP			THREE PLACE .XXX ± 0.005		INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME	REV
		MAXIMUM INRUSH 24 AMP			FOUR PLACE .XXXX ± 0.0005					B	I	1SM61	11
		KEMA, CE 5A, 250V ~ T85 1E4  			THIRD ANGLE PROJECTION		RASTER			SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1
		UL, CSA 5A, 250 VAC  BRAND L4											
		BRAND											