

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-15-013292	24SEP2015	DL	CW
	B1	ECR-16-018198	12FEB2017	QY	CW
	C	ECR-21-105887	26JUL2021	BS	CW
	D	ECR-22-150866	13SEP2022	DL	CW

NOTES:

- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250 V
RATED CURRENT: 10 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 4 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20200X10XX000)




注释:

- 技术参数:
绝缘材料: PC
额定电压: 250V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 4 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 0.14-2.5 mm² (26-14 AWG)
接线类型: 冷压接
- 端子需要单独订购.
(订货号参考图面: T20200X10XX000)





M4 THREAD RECOMMENDED
TIGHTENING TORQUE 1.2Nm
M4螺丝, 推荐锁紧力矩1.2Nm

TYPE-1:T2030422101-000 TE LOGO
类 型-1:T2030422101-000 TE LOGO




4X M3 THREAD RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝, 推荐锁紧力矩0.5Nm



PANEL CUT OUT FOR INSERTS FOR USING
WITHOUT HOODS/HOUSINGS
不使用防护外壳时芯件的安装开孔图

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 18MAR2015	 TE Connectivity		
		CHK CHRIS WANG 18MAR2015			
		APVD XU XIANG 18MAR2015	NAME HDD-042-M		
DIMENSIONS: mm		PRODUCT SPEC 108-137043	SIZE A3 CAGE CODE - DRAWING NO. ©-T2030422101000 RESTRICTED TO		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH -		APPLICATION SPEC 114-137043			
MATERIAL -		WEIGHT -	SCALE 1:1 SHEET 1 OF 2 REV D		
		CUSTOMER DRAWING			

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-







ALL DIMENSIONS ARE SAME AS TYPE 1,
EXCEPT THOSE DEFINED IN THIS TYPE.
除了在本类型中定义的尺寸外，其它尺寸同类型1


NOTES:

SEE SHEET 1



注释:
见页 1



TYPE-2:T2030422101-001 STAINLESS STEEL SCREW,NO LOGO
类 型-2:T2030422101-001 不锈钢螺丝,无LOGO



T2030422101-001	HDD-042-M	HDD-042 MALE INSERT, STAINLESS STEEL SCREW,NO LOGO HDD-042公插,不锈钢螺丝,无LOGO	TYPE-2 类 型-2
T2030422101-000	HDD-042-M	HDD-042 MALE INSERT HDD-042公插	TYPE-1 类 型-1
PART NUMBER 料 号	PART DESCRIPTION 描 述		TYPE 类 型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 18MAR2015	 TE Connectivity			
DIMENSIONS: mm		CHK CHRIS WANG 18MAR2015	NAME HDD-042-M			
		APVD XU XIANG 18MAR2015				
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		
		0 PLC ±-		108-137043		
		1 PLC ±-		APPLICATION SPEC		
2 PLC ±-		114-137043		SIZE		
3 PLC ±-		WEIGHT		CAGE CODE		
4 PLC ±-		FINISH		DRAWING NO		
ANGLES ±-		MATERIAL		RESTRICTED TO		
-		-		A3		
-		-		-		
CUSTOMER DRAWING		SCALE		SHEET		
		1:1		2 OF 2		
		REV		D		