TE Connectivity: Every Connection Counts
© 2016 TE Connectivity Ltd. family of companies. All Rights Reserved

HARNESSING

HEAT SHRINK BOOTS



✔ Active

TE CONNECTIVITY (TE)

202D163-3/86-0

Raychem | CAP , CRPS

202D163-3/86-0
TE Internal Number: 806996-000
Alias ID: 8-1196248-0

EU RoHS Compliant
EU ELV Compliant

Lipped Yes

Operating Temperature Range (°C) -55 – 105

Fluid/Chemical Resistance Suitable for occasional exposure to fluids

Adhesive Options /86 Precoat, -55 – 105°C (-67 – 221°F)

Material Systems Code 10

PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

Boot, Straight, With Lips
PDF
English

Product Specifications

Product Specification

Thermofit Polyolefin Molded Components Flame-Retarded, Semi-Rigid, Heat-Shrinkable
PDF
English

FEATURES

Downloaded from Arrow.com.

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Molded Part Type Molded Boot

Configuration Features

Lipped Yes

Body Features

Material Systems Code 10
Adhesive Pre-Coat Yes
Entry Size (Braided or Magneform Adapter) 15, 16, 18, 20
Entry Size (Solid or Fixed Adapter) 10 – 12
Material Modified Polyolefin
Entry Size (Tinel-Lock Adapter) 14, 16, 18, 20
Entry Size (Spin Coupling Adapter) 16 – 18

Dimensions

Cable Diameter Range 9.9 – 22.1 mm [.39 – .87 in]
Wire/Cable Outside Diameter .43 in, .433 in, .47 in, .55 in, .63 in, .7 in, .71 in, .787 in, 11 mm, 12 mm, 14 mm, 16 mm, 18 mm, 20 mm

Usage Conditions

Operating Temperature Range (°C) -55 – 105

Operation/Application

Power Cable Accessory No

Industry Standards

Government Qualified No
Approved Standards BS-G-198-5-DA, DEF Std 59-97 Issue 3 Type DA, SAE AS I 81765/1, Type I, UL 224, File E85381

Other

Fluid/Chemical Resistance Suitable for occasional exposure to fluids
Adhesive Options /86 Precoat, -55 – 105°C (-67 – 221°F)
Adhesive Type High Performance Pre-Coat Adhesive

Statement of Compliance

Statement of Compliance
PDF

Downloaded from Arrow.com.