

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC
J

DIST
-

REVISIONS

変更

P

LTR

DESCRIPTION

DATE

DWN

APVD






A

RELEASED

01JUL2010

YS

TH



1. APPLICABLE WIRE RANGE;
AVSS 0.3, 0.5, 0.3f, 0.5f
CAVS 0.3, 0.5
CHFUS 0.35, 0.50
HFTUF 2c×0.5
2. APPLICATOR FEED; 18mm

△ 3 TIN PLATING AREA.

1. 適用電線;
AVSS 0.3, 0.5, 0.3f, 0.5f
CAVS 0.3, 0.5
CHFUS 0.35, 0.50
HFTUF 2c×0.5
2. アプリケータ送りピッチ; 18mm

△ 3 すずめっき範囲

1612124-8

PART NUMBER

WIRE RANGE
包合電線断面積 0.37~0.56mm²

INSULATION DIA
被覆外径 ϕ 1.1~1.7mm

Tyco Electronics

Tyco Electronics Corporation
Kawasaki, Japan


NAME
名称 1mm DIA SOCKET CONTACT

SIZE A3 CAGE CODE 00779 DRAWING NO 1612124-8

RESTRICTED TO
-

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
単位: mm



MATERIAL
材料 COPPER Alloy

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差 ±0.2
0-PLC ±
1-PLC ±0.1
2-PLC ±0.01
3-PLC ±0.001
4-PLC ±0.0001
ANGLES ±1.00°

FINISH
仕上 SELECTIVE GOLD

DWN Y. SHINDO 01JUL2010
CHK T. HAYASHI 01JUL2010
APVD H. YAMAGAMI 01JUL2010

PRODUCT SPEC
製品規格
APPLICATION SPEC
取付適用規格
114-5315-2

WEIGHT 0.36g

CUSTOMER DRAWING

SCALE 5:1

SHEET 1 OF 1

REV A