

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BZ-2RW86324-A2

APY6600

BZ-2RW86324-A2

PAGE 1 OF 1

REPLACES X-82424-BZ

RELEASE NO. PR-14125

DRAWING
NUMBER

7

ISSUE

REVISIONS

REV	DATE	BY	CHKD	DESCRIPTION
A	061823	KAG		
B	064294	CO		
C	73287-J	CO		
D	77588	CO		
E	093346	CO		
F	0017579	CO		

CHECK

08DEC05

RJ

08DEC05

3 SEPT 85


08DEC05

08DEC05

08DEC05

08DEC05

08DEC05




NOTES

- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 .002 CENTERS
- SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE - - - - 1 OZ MAX

DIFFERENTIAL TRAVEL - - - .018 - .140

OVERTRAVEL - - - - .500 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

-L96- 15 A-125, 250, OR 480 VAC
1/2 A-125 VDC; 1/4 A-250 VDC
1/8 HP-125 VAC, 1/4 HP-250 VAC

-L288-
-L315-
-L306-

16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DES. UNITS	TOL. mm/in	DES. IN	TOL. mm/in
NO PLACES	X	1/.04	X	0.01/0.005
ONE PLACE	X.X	0.05/0.010	X.X	0.001/0.010
TWO PLACES	X.XX	0.005/0.005	X.XX	0.0001/0.0005
THREE PLACES	X.XXX		X.XXX	

DESIGN UNITS ☐ SI METRIC ☒ US CUSTOMARY

WEIGHT

FORMTEK

FO-52848-A

DRAWN

08DEC05

08DEC05