

MLG0603SR11JT000

Applications		Commercial Grade
Feature		Multilayer
		Non-Magnetic Core (Dielectric Ceramic)
Series	MLG Series / MLG0603S Type	
Status	PROD	



Size	
Length(L)	0.60mm +/-0.03mm
Width(W)	0.30mm +/-0.03mm
Thickness(T)	0.30mm +/-0.03mm
Recommended Land Pattern (A)	0.25mm Nom.
Recommended Land Pattern (B)	0.30mm Nom.
Recommended Land Pattern (C)	0.30mm Nom.

Electrical Characteristics	
Inductance	110nH +/-5% at 100MHz
Rated Current (Temperature Rise) [Max.]	50mA (20degC Rise)
Self-Resonant Frequency [Min.]	770MHz
Self-Resonant Frequency [Typ.]	940MHz
Q [Min.]	5 at 100MHz
Q [Typ.]	7 at 100MHz
DC Resistance [Nom.]	5.24Ω
DC Resistance [Max.]	6.5Ω


Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	15000Pcs Min.
Weight	0.0002g

•This PDF document was created based on the data listed on the TDK Corporation website.


•All specifications are subject to change without notice.

MLG0603SR11JT000


Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




MLG0603SR11JT000



MLG0603SR11JT000



MLG0603SR11JT000




MLG0603SR11JT000

•This PDF document was created based on the data listed on the TDK Corporation website.


•All specifications are subject to change without notice.

MLG0603SR11JT000

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)



MLG0603SR11JT000(Amb. Temp. = 20degC)



•This PDF document was created based on the data listed on the TDK Corporation website.

•All specifications are subject to change without notice.