

# GPS3326

## Internal Active GPS Antenna

### Features

- ♦ Very Compact internal GPS patch
- ♦ 13.4 x 13.4 mm dimensions
- ♦ Various cable/connector options
- ♦ 26 dB LNA gain

### Specifications

Specifications	
Radiating element	Patch
Frequency range	1575.42 +/- 1.023 MHz
Effective gain	26 dB incl. LNA
Polarisation	RHCP
Operating Voltage	2.8-3.3V
Power consumption	10mA typical
Output Impedance	50 Ohm
Noise Figure	1.5 dB typical
Cable / Connector	100mm cable and IPEX (U.FL)
Dimensions	13.4 x 13.4 x 5.5mm

### Popular Ordering Options

FGPS35228-IPX-10	GPS3326 with 100mm cable and IPX Connector
------------------	--

Specifications subject to change without notice.

5 Little Balmer  
Buckingham Industrial Park  
Buckingham  
MK18 1TF  
UK

Tel: +44 (0)1280 824055  
Fax: +44 (0)1280 817179  
Email: [sales@ead-ltd.com](mailto:sales@ead-ltd.com)  
Web: [www.ead-ltd.com](http://www.ead-ltd.com)

**EAD**  
embedded antenna design ltd  
*Delivering Antenna Innovation*